




DUAL-IN-LINE SOCKETS

SERIES 214 • SURFACE MOUNT, AUTO PLACEMENT, STUB TAIL • CLOSED FRAME



- Unique floating contacts compensate for the effects of unevenly screened solder paste
- Available packaged in tubes or on tape & reel per EIA-481
- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 253 for details
- Series 214 uses MM #1434 pins. See page 162 for details
- High temp. Nylon 46 insulator is suitable for all surface mount soldering processes. Closed frame insulator is vision system compatible
- For Electrical, Mechanical and Environmental Data, see page 264 for details



Total number of pins 				Quantity per tube	ORDERING INFORMATION								
					Tube Packaging	Tape & Reel Packaging	Tape Width (mm)	QTY per Reel					
VACUUM PAD TOP SURFACE ONLY					214-XX-306-01-670800	214-XX-306-01-670799	16	750					
					214-XX-308-01-670800	214-XX-308-01-670799	16	1000					
					214-XX-314-01-670800	214-XX-314-01-670799	32	750					
					214-XX-316-01-670800	214-XX-316-01-670799	32	750					
					214-XX-318-01-670800	214-XX-318-01-670799	44	750					
					214-XX-320-01-670800	214-XX-320-01-670799	44	750					
					VACUUM PAD TOP AND BOTTOM					214-XX-624-01-670800	214-XX-624-01-670799	44	400
										214-XX-628-01-670800	214-XX-628-01-670799	56	400
										214-XX-632-01-670800	214-XX-632-01-670799	56	400
										214-XX-640-01-670800	NOT AVAILABLE		
XX=Plating Code See Below RoHS-2 2011/65/EU													
SPECIFY PLATING CODE XX =						99		44					
Sleeve (Pin) 						5,08µm Sn/Pb		5,08µm Sn					
Contact (Clip) 						2,54µm Sn/Pb		2,54µm Sn					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[214-44-306-01-670799](#) [214-44-316-01-670799](#) [214-99-316-01-670799](#) [214-44-306-01-670800](#)