

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0026605090

Status:

Active

Overview:

KK Interconnect Solutions

Description:

KK 396 Header, Right-Angle with Friction Lock, 9 Circuits, Tin (Sn) Plating

Documents:

- Drawing (PDF)

Packaging Specification PK-41792-002-001 (PDF)
- 3D Model

Symbol Footprint Data SYM-26-60-5090-001 (PDF)
- 3D Model (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-08-50-001 (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Headers

Series

41792

Application

Power, Wire-to-Board

Overview

KK Interconnect Solutions

Product Name

KK 396

UPC

800753688551

Physical

Breakaway

No

Circuits (Loaded)

9

Circuits (maximum)

9

Color - Resin

Natural

Durability (mating cycles max)

25

Flammability

94V-0

Glow-Wire Capable

No

Lock to Mating Part

Yes

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Resin

Polyester

Net Weight

4.285/g

Number of Rows

1

Orientation

Right Angle

PC Tail Length

3.96mm

PCB Locator

No

PCB Retention

None

PCB Thickness - Recommended

1.60mm

Packaging Type

Bag

Pitch - Mating Interface

3.96mm

Polarized to Mating Part

Yes

Polarized to PCB

No

Shrouded

Partial

Stackable

Yes

Temperature Range - Operating

See Product Specification

Termination Interface: Style

Through Hole

Electrical

Current - Maximum per Contact

7.0A

Voltage - Maximum

250V

Solder Process Data

Duration at Max. Process Temperature (seconds)

005

Lead-freeProcess Capability

WAVE



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

41792 Series

Mates With

2139 KK Crimp Housing, 41695 KK Crimp
Housing, 6442 KK Crimp Housing, 2145
PCB Connector, 41815 PCB Connector,
3069 KK Crimp Housing

Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235
Material Info	
Engineering Number	41792-0009
Reference - Drawing Numbers	
Packaging Specification	PK-41792-002-001
Product Specification	PS-08-50-001
Sales Drawing	SDA-41792-000
Symbol/Footprint Data	SYM-26-60-5090-001

This document was generated on 09/30/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

26-60-5090