



0660



0660-0-15-XX-30-XX-10-0

Solder mount in .051 min. mounting hole


0677



0677-0-15-XX-30-XX-10-0

Solder mount in .051 min. mounting hole


0555



0555-0-15-XX-20-XX-10-0

Solder mount in .053 min. mounting hole


0558



0558-0-15-XX-30-XX-10-0

Solder mount in .061 min. mounting hole

0675/0679




067X-0-15-XX-30-XX-10-0

Solder mount in .054 min. mounting hole

Basic Part Number	Length L
0675-0	.145
0679-0	.203

1065/1066/7065




X06X-0-15-XX-30-XX-10-0

Solder mount in .055 min. mounting hole

Basic Part Number	Length L
1065-0	.190
1066-0	.160
7065-0	.181


0682



0682-0-15-XX-32-XX-10-0

Solder mount in .056 min. mounting hole


0667



0667-0-15-XX-30-XX-10-0

Solder mount in .057 min. mounting hole


0665



0665-0-15-XX-30-XX-10-0

Solder mount in .061 min. mounting hole

4286



4286-0-15-XX-30-XX-10-0

Hex press-fit in .055 plated thru hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: $\pm .005$
DIAMETERS: $\pm .002$
ANGLES: $\pm .002^\circ$

ORDER CODE: XXXX - X - 15 - XX - XX - XX - 10 - 0

BASIC PART #
SPECIFY SHELL FINISH:
01 200 μ " TIN/LEAD OVER NICKEL
15 10 μ " GOLD OVER NICKEL

SPECIFY CONTACT FINISH:
02 200 μ " TIN/LEAD OVER NICKEL
14 10 μ " GOLD OVER NICKEL
27 30 μ " GOLD OVER NICKEL

SELECT CONTACT

#30 or #32 CONTACT (DATA ON PAGE 208)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[0558-0-15-15-30-14-10-0](#) [7065-0-15-15-30-14-10-0](#) [1066-0-15-15-30-14-10-0](#) [0675-0-15-15-30-14-10-0](#)