


## 0327/0351/0373




| Basic Part Number | Length L | Depth N |
|-------------------|----------|---------|
| 0327-0            | .206     | .180    |
| 0351-0            | .226     | .200    |
| 0373-0            | .270     | .241    |

**03XX-0-15-XX-34-XX-10-0**

Solder mount in .075 min. mounting hole


## 0328



**0328-0-15-XX-34-XX-10-0**

Hex press-fit in .079 plated thru hole


## 0334



**0334-0-15-XX-34-XX-10-0**

Hex press-fit in .079 plated thru hole


## 0312



**0312-0-15-XX-34-XX-10-0**

Solder mount in .075 min. mounting hole


## 0333



**0333-0-42-XX-34-XX-10-0**

Press-fit in .076 mounting hole


## 0357



**0357-0-15-XX-34-XX-10-0**

Press-fit in .078 mounting hole


## 0317



**0317-0-15-XX-34-XX-10-0**

Solder mount in .091 min. mounting hole


## 0340



**0340-0-15-XX-34-XX-10-0**

Solder mount in .087 min. mounting hole


## 0345



**0345-0-15-XX-34-XX-10-0**

Press-fit in .089 mounting hole


## 0316



**0316-0-15-XX-34-XX-10-0**

Solder mount in .087 min. mounting hole

## 0314



**0314-0-15-XX-34-XX-10-0**

Solder mount in .087 min. mounting hole

### SPECIFICATIONS

**SHELL MATERIAL:**  
Brass Alloy 360, 1/2 Hard

**CONTACT MATERIAL:**  
Beryllium Copper Alloy 172, HT

**DIMENSION IN INCHES**  
**TOLERANCES ON:**  
LENGTHS: ±.005  
DIAMETERS: ±.002  
ANGLES: ± 2°

**ORDER CODE: XXXX - X - XX - XX - 34 - XX - 10 - 0**

**BASIC PART #**

**SPECIFY SHELL FINISH:**

01 200μ" TIN/LEAD OVER NICKEL

15 10μ" GOLD OVER NICKEL

**SPECIFY CONTACT FINISH:**

01 200μ" TIN/LEAD OVER NICKEL

14 10μ" GOLD OVER NICKEL

27 30μ" GOLD OVER NICKEL

**CONTACT**

#34 CONTACT (DATA ON PAGE 212)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[0351-0-15-15-34-14-10-0](#) [0328-0-15-15-34-14-10-0](#)