




OPTION D



SECTION C-C



- NOTES:
1. MATERIAL: HOUSING - G.F. POLYESTER, 94V-0
TERMINAL - PHOSPHOR BRONZE
 2. FINISH: 0.38 MICROMETERS/15 MICROINCHES MINIMUM GOLD IN SELECT AREA
1.91 MICROMETERS/75 MICROINCHES MINIMUM TIN IN SELECT AREA
OVER NICKEL UNDERPLATE OVER-ALL.
 3. PRODUCT SPECIFICATION: PS-70400
 4. TO BE USED WITH 26 AWG. STANDARD WIRE WITH 1.35/.053 DIAMETER MAXIMUM INSULATION.
 5. SEE CHART FOR CIRCUIT SIZES.
 6. STANDARD PACKAGING PER PK-70873-0001. OPTIONAL PACKAGING MAY BE AVAILABLE, REQUEST DRAWING PK-70475.
 7. PARTS STACKABLE END TO END ON 2.54/.100 CENTERS
 8. SEE DRAWING SDA-70457-**** (SHEET 3) FOR OPTIONAL HOUSING DETAILS.
 9. 4 CIRCUIT SHOWN. 3-25 CIRCUITS HAVE 2 RIBS.
 10. TO MATE WITH MOLEX PART NUMBERS: 70018-0000, 70022-****, 70104-****.
 11. 2 CIRCUIT ASSEMBLIES SUPPLIED AS GROUPED PAIRS.

CKT. SIZE	A	B	EDP. NO.	ENG. NO.
2	(2.54) .100	(5.05) .199	I4-44-I602	A-70475-0771
3	(5.08) .200	(7.59) .299	I4-44-I603	A-70475-0772
4	(7.62) .300	(10.13) .399	I4-44-I604	A-70475-0773
5	(10.16) .400	(12.67) .499	I4-44-I605	A-70475-0774
6	(12.70) .500	(15.21) .599	I4-44-I606	A-70475-0775
7	(15.24) .600	(17.75) .699	I4-44-I607	A-70475-0776
8	(17.78) .700	(20.29) .799	I4-44-I608	A-70475-0777
9	(20.32) .800	(22.83) .899	I4-44-I609	A-70475-0778
10	(22.86) .900	(25.37) .999	I4-44-I610	A-70475-0779
11	(25.54) 1.000	(27.91) 1.099	I4-44-I611	A-70475-0780
12	(27.94) 1.100	(30.45) 1.199	I4-44-I612	A-70475-0781
13	(30.48) 1.200	(32.99) 1.299	I4-44-I613	A-70475-0782
14	(33.02) 1.300	(35.53) 1.399	I4-44-I614	A-70475-0783
15	(35.56) 1.400	(38.07) 1.499	I4-44-I615	A-70475-0784
16	(38.01) 1.500	(40.61) 1.599	I4-44-I616	A-70475-0785
17	(40.64) 1.600	(43.15) 1.699	I4-44-I617	A-70475-0786
18	(43.18) 1.700	(45.69) 1.799	I4-44-I618	A-70475-0787
19	(45.72) 1.800	(48.23) 1.899	I4-44-I619	A-70475-0788
20	(48.26) 1.900	(50.77) 1.999	I4-44-I620	A-70475-0789
21	(50.80) 2.000	(53.31) 2.099	I4-44-I621	A-70475-0790
22	(53.34) 2.100	(55.85) 2.199	I4-44-I622	A-70475-0791
23	(55.88) 2.200	(58.39) 2.299	I4-44-I623	A-70475-0792
24	(58.42) 2.300	(60.93) 2.399	I4-44-I624	A-70475-0793
25	(60.96) 2.400	(63.47) 2.499	I4-44-I625	A-70475-0794



I.D. SLOT CODE TO WIRE GAUGE CHART	
I.D. SLOT CODE	WIRE GAUGE
B	26 AWG.

PLATING CODE (STRIPE ON CARRIER STRIP)	
PLATING	COLOR
I5 GOLD	YELLOW

ADD GEN TOLERANCES EC NO: UCP2011-3892 DRWN:MSI BARRA 2011/06/27 CHKD:DMORGAN APPR:SMILLER 2011/07/07	DESCRIPTION	QUALITY SYMBOLS F=0 E=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	TITLE ASSEMBLY, SL CONNECTOR SINGLE ROW 2.54/.100 GRID MOLEX MOLEX INCORPORATED
						DRAWN BY WAZ	DATE 10/13/84				
						CHECKED BY WAZ	DATE 10/13/84				
						APPROVED BY RL	DATE 10/13/84				
						MATERIAL NO.			DOCUMENT NO.		
			ANGULAR ±1/2°			SEE TABLE		SDA-70475-0771-0794		1 OF 1	
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								
						THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

14-44-1615