




OPTION D



SECTION C-C



HOUSING PART NO. 70066-****
TERMINAL PART NO. 70110-****

- NOTES:
1. MATERIAL: HOUSING - G.F. POLYESTER, 94V-0
TERMINAL - PHOSPHOR BRONZE
 2. FINISH: 0.38 MICROMETERS/15 MICROINCHES MINIMUM GOLD IN SELECT AREA
1.91 MICROMETERS/75 MICROINCHES MINIMUM TIN IN SELECT AREA
OVER NICKEL UNDERPLATE OVER-ALL.
 3. PRODUCT SPECIFICATION: PS-70400
 4. TO BE USED WITH 26 AWG. STANDARD WIRE WITH 1.35/.053 DIAMETER MAXIMUM INSULATION.
 5. SEE CHART FOR CIRCUIT SIZES.
 6. STANDARD PACKAGING PER PK-70873-0001. OPTIONAL PACKAGING MAY BE AVAILABLE, REQUEST DRAWING PK-70475.
 7. PARTS STACKABLE END TO END ON 2.54/.100 CENTERS
 8. SEE DRAWING SDA-70457-**** (SHEET 3) FOR OPTIONAL HOUSING DETAILS.
 9. 4 CIRCUIT SHOWN. 3-25 CIRCUITS HAVE 2 RIBS.
 10. TO MATE WITH MOLEX PART NUMBERS: 70018-0000, 70022-****, 70104-****.
 11. 2 CIRCUIT ASSEMBLIES SUPPLIED AS GROUPED PAIRS.

CKT. SIZE	A	B	EDP. NO.	ENG. NO.
2	(2.54) .100	(5.05) .199	I4-44-I602	A-70475-0771
3	(5.08) .200	(7.59) .299	I4-44-I603	A-70475-0772
4	(7.62) .300	(10.13) .399	I4-44-I604	A-70475-0773
5	(10.16) .400	(12.67) .499	I4-44-I605	A-70475-0774
6	(12.70) .500	(15.21) .599	I4-44-I606	A-70475-0775
7	(15.24) .600	(17.75) .699	I4-44-I607	A-70475-0776
8	(17.78) .700	(20.29) .799	I4-44-I608	A-70475-0777
9	(20.32) .800	(22.83) .899	I4-44-I609	A-70475-0778
10	(22.86) .900	(25.37) .999	I4-44-I610	A-70475-0779
11	(25.54) 1.000	(27.91) 1.099	I4-44-I611	A-70475-0780
12	(27.94) 1.100	(30.45) 1.199	I4-44-I612	A-70475-0781
13	(30.48) 1.200	(32.99) 1.299	I4-44-I613	A-70475-0782
14	(33.02) 1.300	(35.53) 1.399	I4-44-I614	A-70475-0783
15	(35.56) 1.400	(38.07) 1.499	I4-44-I615	A-70475-0784
16	(38.01) 1.500	(40.61) 1.599	I4-44-I616	A-70475-0785
17	(40.64) 1.600	(43.15) 1.699	I4-44-I617	A-70475-0786
18	(43.18) 1.700	(45.69) 1.799	I4-44-I618	A-70475-0787
19	(45.72) 1.800	(48.23) 1.899	I4-44-I619	A-70475-0788
20	(48.26) 1.900	(50.77) 1.999	I4-44-I620	A-70475-0789
21	(50.80) 2.000	(53.31) 2.099	I4-44-I621	A-70475-0790
22	(53.34) 2.100	(55.85) 2.199	I4-44-I622	A-70475-0791
23	(55.88) 2.200	(58.39) 2.299	I4-44-I623	A-70475-0792
24	(58.42) 2.300	(60.93) 2.399	I4-44-I624	A-70475-0793
25	(60.96) 2.400	(63.47) 2.499	I4-44-I625	A-70475-0794



I.D. SLOT CODE TO WIRE GAUGE CHART	
I.D. SLOT CODE	WIRE GAUGE
B	26 AWG.

PLATING CODE (STRIPE ON CARRIER STRIP)	
PLATING	COLOR
I5 GOLD	YELLOW

ADD GEN TOLERANCES EC NO: UCP2011-3892 DRWN:MSI BARRA 2011/06/27 CHKD:DMORGAN APPR:SMILLER 2011/07/07	DESCRIPTION	QUALITY SYMBOLS F=0 E=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	TITLE ASSEMBLY, SL CONNECTOR SINGLE ROW 2.54/.100 GRID MOLEX MOLEX INCORPORATED	
				mm	INCH	DRAWN BY WAZ	DATE 10/13/84	TITLE			
			4 PLACES	± ---	± ---	CHECKED BY	DATE				
			3 PLACES	± ---	± .010	WAZ	10/13/84				
			2 PLACES	± 0.25	± .014	APPROVED BY	DATE				
		1 PLACE		± 0.35	± ---	RL	10/13/84				
				ANGULAR ±1/2°							
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE TABLE		DOCUMENT NO. SDA-70475-0771-0794		SHEET NO. 1 OF 1	
						SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

14-44-1617