





Fig. 1

- Elevated socket strips are available in 5 different standoff heights:
416...006 uses pin # 0153-1
416...003 uses pin # 0153-2
416...007 uses pin # 0153-3
416...008 uses pin # 0153-4
416...001 uses pin # 0153-5
See page 138 for details.
- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 218 for details.
- Insulators are high temp. thermoplastic.



Ordering Information

Fig. 1

Series 416...006 Standoff Height = 5,99

416-XX-2_ -41-006000

Specify # of pins → 02-64

Fig. 2

Series 416...003 Standoff Height = 8,0

416-XX-2_ -41-003000

Specify # of pins → 02-64

Fig. 3

Series 416...007 Standoff Height = 10,21

416-XX-2_ -41-007000

Specify # of pins → 02-64

Fig. 4

Series 416...008 Standoff Height = 11,99

416-XX-2_ -41-008000

Specify # of pins → 02-64

Fig. 5

Series 416...001 Standoff Height = 15,09

416-XX-2_ -41-001000

Specify # of pins → 02-64




Fig. 2




Fig. 3




Fig. 4




Fig. 5

For Electrical,
Mechanical & Environmental
Data, See pg. 4

XX=Plating Code
See Below

For RoHS compliance
select ◇ plating code.

SPECIFY PLATING CODE XX=		93		43◇
Sleeve (Pin)		5,08µm Sn/Pb		5,08µm Sn
Contact (Clip)		0,76µm Au		0,76µm Au

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[416-43-202-41-006000](#) [416-43-202-41-007000](#) [416-43-202-41-001000](#) [416-93-202-41-001000](#) [416-43-202-41-003000](#) [416-43-202-41-008000](#) [416-93-202-41-007000](#) [416-93-202-41-003000](#) [416-93-202-41-006000](#) [416-93-202-41-008000](#)