



OPTION D

NOTES:


1. MATERIAL: HOUSING - G.F. POLYESTER, 94V-0
TERMINAL - PHOSPHOR BRONZE
2. FINISH: 0.38 MICROMETERS/15 MICROINCHES MINIMUM GOLD
IN SELECT AREA
1.91 MICROMETERS/75 MICROINCHES MINIMUM TIN
IN SELECT AREA
OVER NICKEL UNDERPLATE OVER-ALL.
3. PRODUCT SPECIFICATION: PS-70400
4. TO BE USED WITH 24 AWG. STANDARD WIRE WITH
1.35/.053 DIAMETER MAXIMUM INSULATION.
5. SEE CHART FOR CIRCUIT SIZES.
6. STANDARD PACKAGING PER PK-70873-0001. OPTIONAL
PACKAGING MAY BE AVAILABLE, REQUEST DRAWING
PK-70475.
7. PARTS STACKABLE END TO END ON 2.54/100 CENTERS
8. SEE DRAWING SDA-70457-**** (SHEET 3) FOR OPTIONAL
HOUSING DETAILS.
9. 4 CIRCUIT SHOWN. 3-25 CIRCUITS HAVE 2 RIBS.
10. TO MATE WITH MOLEX PART NUMBERS: 70018-0000,
70022-****, 70104-****.
11. 2 CIRCUIT ASSEMBLIES SUPPLIED AS GROUPED PAIRS.




CIRCUIT NO. 1
IDENTIFICATION
SLOT OR ARROW



SECTION C-C



PRE-LOADED
ASSEMBLY



HOUSING PART NO. 70066-****

TERMINAL PART NO. 70110-****

CKT. SIZE	A	B	EDP. NO.	ENG. NO.
2	(2.54) .100	(5.05) .199	14-44-5302	A-70475-2346
3	(5.08) .200	(7.59) .299	14-44-5303	A-70475-2347
4	(7.62) .300	(10.13) .399	14-44-5304	A-70475-2348
5	(10.16) .400	(12.67) .499	14-44-5305	A-70475-2349
6	(12.70) .500	(15.21) .599	14-44-5306	A-70475-2350
7	(15.24) .600	(17.75) .699	14-44-5307	A-70475-2351
8	(17.78) .700	(20.29) .799	14-44-5308	A-70475-2352
9	(20.32) .800	(22.83) .899	14-44-5309	A-70475-2353
10	(22.86) .900	(25.37) .999	14-44-5310	A-70475-2354
11	(25.54) 1.000	(27.91) 1.099	14-44-5311	A-70475-2355
12	(27.94) 1.100	(30.45) 1.199	14-44-5312	A-70475-2356
13	(30.48) 1.200	(32.99) 1.299	14-44-5313	A-70475-2357
14	(33.02) 1.300	(35.53) 1.399	14-44-5314	A-70475-2358
15	(35.56) 1.400	(38.07) 1.499	14-44-5315	A-70475-2359
16	(38.01) 1.500	(40.61) 1.599	14-44-5316	A-70475-2360
17	(40.64) 1.600	(43.15) 1.699	14-44-5317	A-70475-2361
18	(43.18) 1.700	(45.69) 1.799	14-44-5318	A-70475-2362
19	(45.72) 1.800	(48.23) 1.899	14-44-5319	A-70475-2363
20	(48.26) 1.900	(50.77) 1.999	14-44-5320	A-70475-2364
21	(50.80) 2.000	(53.31) 2.099	14-44-5321	A-70475-2365
22	(53.34) 2.100	(55.85) 2.199	14-44-5322	A-70475-2366
23	(55.88) 2.200	(58.39) 2.299	14-44-5323	A-70475-2367
24	(58.42) 2.300	(60.93) 2.399	14-44-5324	A-70475-2368
25	(60.96) 2.400	(63.47) 2.499	14-44-5325	A-70475-2369



I.D. SLOT CODE TO WIRE GAUGE CHART	
I.D. SLOT CODE	WIRE GAUGE
D	22 AWG.

PLATING CODE (STRIPE ON CARRIER STRIP)	
PLATING	COLOR
15 GOLD	YELLOW

MODIFY PRODUCT SPEC EC NO: UCP2010-0987 DRWN:MSBARRA 2010/01/04 CHKD:JORGAN 2010/01/08 APPR:SMILLER 2010/01/11 REV	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
		▽=0 ▽=0 ▽=0	mm INCH	DRAWN BY AAB	DATE 11/30/1987	TITLE ASSEMBLY, SL CONNECTOR SINGLE ROW 2.54/100 GRID				
			4 PLACES ± --- ± ---	CHECKED BY	DATE					
			3 PLACES ± --- ± .010	APPROVED BY	DATE	MOLEX MOLEX INCORPORATED				
			2 PLACES ± 0.25 ± .014	WAZ	11/30/1987					
1 PLACE ± 0.35 ± ---	ANGULAR ±1/2°		MATERIAL NO.	DOCUMENT NO.	SHEET NO.					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE		SDA-70475-2346-2369		1 OF 1			
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

14-44-5321