

INTERCONNECTS

SERIES 714...01X • 2,54 GRID ULTRA LOW PROFILE CARRIERS • SINGLE AND DOUBLE ROW STRIPS




FIG. 1




FIG. 2




FIG. 3





FIG. 4

- Ultra low profile receptacles sit 0,46 above the board
- Series 714 use MM #0552-1 and MM #0552-2 pin receptacles. See page 158 for details
- Hi-Rel, 3-finger BeCu #11 contact is rated at 3 amps. See page 251 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Single Row (0,99 min. mounting hole)	
	714-XX-1	-31-012000
	Specify number of pins	01-64
FIG. 2	Single Row (0,99 min. mounting hole)	
	714-XX-1	-31-018000
	Specify number of pins	01-64
FIG. 3	Double Row (0,99 min. mounting hole)	
	714-XX-2	-31-012000
	Specify number of pins	04-64
FIG. 4	Double Row (0,99 min. mounting hole)	
	714-XX-2	-31-018000
	Specify number of pins	04-64
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Environmental Data, See page 264		
SPECIFY PLATING CODE XX=		
Sleeve (Pin)	91	93
Contact (Clip)	41	43
	5,08µm Sn/Pb	5,08µm Sn
	0,25µm Au	0,76µm Au

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[714-91-103-31-018000](#) [714-91-164-31-018000](#) [714-91-101-31-018000](#) [714-91-132-31-018000](#) [714-91-102-31-018000](#) [714-91-132-31-012000](#) [714-93-102-31-018000](#) [714-93-101-31-018000](#) [714-41-101-31-018000](#) [714-41-103-31-018000](#) [714-41-132-31-012000](#) [714-91-264-31-012000](#) [714-93-104-31-018000](#) [714-41-102-31-018000](#) [714-91-264-31-018000](#) [714-41-264-31-018000](#) [714-41-132-31-018000](#) [714-41-264-31-012000](#) [714-41-164-31-018000](#) [714-43-112-31-012000](#) [714-41-164-31-012000](#)