

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0151350605
Status: Active
Overview: CLIK-Mate Wire-to-Board Connectors
Description: CLIK-Mate-to-CLIK-Mate Off-the-Shelf (OTS) Cable Assembly, Single Row, 450.00mm Length, 6 Circuits, Beige

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General
Product Family Cable Assemblies
Series 15135
Application Signal, Wire-to-Board
Assembly Configuration Dual Ended Connectors
Connector to Connector CLIK-Mate-to-CLIK-Mate
Overmolded No
Overview CLIK-Mate Wire-to-Board Connectors
Product Name CLIK-Mate
Type Discrete Wire Assembly
UPC 191128160346

Physical
Cable Length 450.00mm
Circuits (Loaded) 6
Color - Resin Beige
Gender Male-Male
Lock to Mating Part Yes
Material - Metal Copper Alloy
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin PBT
Net Weight 9.260/g
Number of Rows 1
Packaging Type Bag
Pitch - Mating Interface 1.50mm
Plating min - Mating 0.406µm
Plating min - Termination 0.406µm
Single Ended No
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 1.10mm
Wire Size AWG 24
Wire/Cable Type UL 1061

Electrical
Current - Maximum per Contact 2.0A
Voltage - Maximum 100V AC (RMS)/DC

Material Info

Reference - Drawing Numbers
Sales Drawing 2012341677-000



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2021)4569-DC (8
July 2021)
Halogen-Free
Status
Not Low-Halogen
For more information, please visit [Contact US](#)

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series
15135 Series

Mates With
Bottom-Entry Receptacle 503395 . Right
Angle, Through Hole Receptacle 503175
. Right Angle, Surface Mount Receptacle
502585 . Vertical, Through Hole Receptacle
503159 . Vertical, Surface Mount Receptacle
502584

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15135-0605](#)