MITSUBISHI ELECTRIC

<IGBT Modules>

CM600DY-24T

HIGH POWER SWITCHING USE
INSULATED TYPE

dual switch (half-bridge)

Collector current I_C ..... **600** A
Collector-emitter voltage V_{CES} ..... **1200** V
Maximum junction temperature T_{vjmax} ..... **175** °C

- Flat base type
- Nickel-plating tab terminals
- RoHS Directive compliant
- UL Recognized under UL1557, File No.E323585

APPLICATION

AC Motor Control, Motion/Servo Control, Power supply, etc.

OPTION (Below options are available.)

- PC-TIM (Phase Change Thermal Interface Material) pre-apply (Note8)
- V_{CEsat} selection for parallel connection

OUTLINE DRAWING & INTERNAL CONNECTION

Dimension in mm



INTERNAL CONNECTION



Tolerance otherwise specified

Division of Dimension		Tolerance
0.5	to 3	±0.2
over 3	to 6	±0.3
over 6	to 30	±0.5
over 30	to 120	±0.8
over 120	to 400	±1.2

JIS B 0405 c

MAXIMUM RATINGS (T_{vj}=25 °C, unless otherwise specified)

Symbol	Item	Conditions	Rating	Unit
V_{CES}	Collector-emitter voltage	G-E short-circuited	1200	V
V_{GES}	Gate-emitter voltage	C-E short-circuited	± 20	V
I_C	Collector current	DC, T_C=144 °C* (Note2, 4)	600	A
I_{CRM}		Pulse, Repetitive (Note3)	1200	
P_{tot}	Total power dissipation	T_C=25 °C (Note2, 4)	6250	W
I_E (Note1)	Emitter current	DC (Note2)	600	A
I_{ERM} (Note1)		Pulse, Repetitive (Note3)	1200	
V_{isol}	Isolation voltage	Terminals to base plate, RMS, f=60 Hz, AC 1 min	4000	V
T_{jmax}	Maximum junction temperature	Instantaneous event (overload) (Note8)	175	°C
T_{Cmax}	Maximum case temperature	(Note4,8)	150*	
T_{jop}	Operating junction temperature	Continuous operation (under switching) (Note8)	-40 ~ +150	°C
T_{stg}	Storage temperature	-	-40 ~ +150*	

ELECTRICAL CHARACTERISTICS (T_{vj}=25 °C, unless otherwise specified)

Symbol	Item	Conditions		Limits			Unit
				Min.	Typ.	Max.	
I_{CES}	Collector-emitter cut-off current	V_{CE}=V_{CES}, G-E short-circuited		-	-	1.0	mA
I_{GES}	Gate-emitter leakage current	V_{GE}=V_{GES}, C-E short-circuited		-	-	0.5	μA
$V_{GE(th)}$	Gate-emitter threshold voltage	I_C=60 mA, V_{CE}=10 V		5.4	6.0	6.6	V
V_{CEsat} (Terminal)	Collector-emitter saturation voltage	I_C=600 A, V_{GE}=15 V, Refer to the figure of test circuit (Note5)	T_{vj}=25 °C	-	1.75	2.05	V
			T_{vj}=125 °C	-	2.00	-	
			T_{vj}=150 °C	-	2.10	-	
V_{CEsat} (Chip)		I_C=600 A, V_{GE}=15 V, (Note5)	T_{vj}=25 °C	-	1.55	1.80	V
			T_{vj}=125 °C	-	1.75	-	
			T_{vj}=150 °C	-	1.80	-	
C_{ies}	Input capacitance	V_{CE}=10 V, G-E short-circuited		-	-	123	nF
C_{oes}	Output capacitance			-	-	3.6	
C_{res}	Reverse transfer capacitance			-	-	1.5	
Q_G	Gate charge	V_{CC}=600 V, I_C=600 A, V_{GE}=15 V		-	3.7	-	μC
$t_{d(on)}$	Turn-on delay time	V_{CC}=600 V, I_C=600 A, V_{GE}=±15 V, R_G=1.0 Ω, Inductive load		-	-	500	ns
t_r	Rise time			-	-	200	
$t_{d(off)}$	Turn-off delay time			-	-	600	
t_f	Fall time			-	-	300	
V_{EC} (Note.1) (Terminal)	Emitter-collector voltage	I_E=600 A, G-E short-circuited, Refer to the figure of test circuit (Note5)	T_{vj}=25 °C	-	1.85	2.25	V
			T_{vj}=125 °C	-	2.00	-	
			T_{vj}=150 °C	-	2.00	-	
V_{EC} (Note.1) (Chip)		I_E=600 A, G-E short-circuited, (Note5)	T_{vj}=25 °C	-	1.65	2.00	V
			T_{vj}=125 °C	-	1.65	-	
			T_{vj}=150 °C	-	1.65	-	
t_{rr} (Note1)	Reverse recovery time	V_{CC}=600 V, I_E=600 A, V_{GE}=±15 V, R_G=1.0 Ω, Inductive load		-	-	400	ns
Q_{rr} (Note1)	Reverse recovery charge			-	60	-	μC
E_{on}	Turn-on switching energy per pulse	V_{CC}=600 V, I_C=I_E=600 A, V_{GE}=±15 V, R_G=1.0 Ω, T_{vj}=150 °C, Inductive load		-	56.6	-	mJ
E_{off}	Turn-off switching energy per pulse			-	64.3	-	
E_{rr} (Note1)	Reverse recovery energy per pulse			-	38.2	-	mJ
$R_{CC'+EE'}$	Internal lead resistance	Main terminals-chip, per switch, T_C=25 °C (Note4)		-	0.3	-	mΩ
r_g	Internal gate resistance	Per switch		-	0.67	-	Ω

*: The value of PC-TIM applied module is limited by the heat resistant temperature of PC-TIM.

THERMAL RESISTANCE CHARACTERISTICS

Symbol	Item	Conditions		Limits			Unit
				Min.	Typ.	Max.	
$R_{th(j-c)Q}$	Thermal resistance	Junction to case, per Inverter IGBT (Note4)		-	-	24	K/kW
$R_{th(j-c)D}$		Junction to case, per Inverter FWD (Note4)		-	-	42	
$R_{th(c-s)}$	Contact thermal resistance	Case to heat sink, per 1 module	Thermal grease applied (Note4,6,8)	-	13.3	-	K/kW

MECHANICAL CHARACTERISTICS

Symbol	Item	Conditions		Limits			Unit
				Min.	Typ.	Max.	
M_t	Mounting torque	Main terminals	M 6 screw	3.5	4.0	4.5	N·m
M_s	Mounting torque	Mounting to heat sink	M 6 screw	3.5	4.0	4.5	N·m
d_s	Creepage distance	Terminal to terminal		17.3	-	-	mm
		Terminal to base plate		25.3	-	-	
d_a	Clearance	Terminal to terminal		12.6	-	-	mm
		Terminal to base plate		21.8	-	-	
e_c	Flatness of base plate	On the centerline X, Y (Note7)		±0	-	+200	μm
m	mass	-		-	260	-	g

*: This product is compliant with the Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment (RoHS) directive 2011/65/EU and (EU) 2015/863.EU.

Note1. Represent ratings and characteristics of the anti-parallel, emitter-collector free-wheeling diode (FWD).

2. Junction temperature (T_{vj}) should not increase beyond T_{vjmax} rating.
3. Pulse width and repetition rate should be such that the device junction temperature (T_{vj}) dose not exceed T_{vjmax} rating.
4. Case temperature (T_C) and heat sink temperature (T_S) are defined on the each surface (mounting side) of base plate and heat sink just under the chips. Refer to the figure of chip location.
5. Pulse width and repetition rate should be such as to cause negligible temperature rise. Refer to the figure of test circuit.
6. Typical value is measured by using thermally conductive grease of λ=3.0 W/(m·K)/$D_{(C-S)}$=50 μm.
7. The base plate (mounting side) flatness measurement points (X, Y) are shown in the following figure.



8. Long term performance related to thermal conductive grease and PC-TIM (including but not limited to aspects such as the increase of thermal resistance due to pumping out, etc.) should be verified under your specific application conditions. Each temperature condition ($T_{vj\,max}$, $T_{vj\,op}$, $T_{C\,max}$) must be maintained below the maximum rated temperature throughout consideration of the temperature rise even for long term usage.

RECMENDED OPERATING CONDITIONS

Symbol	Item	Conditions	Limits			Unit
			Min.	Typ.	Max.	
V_{CC}	(DC) Supply voltage	Applied across C1-E2 terminals	-	600	850	V
V_{GEon}	Gate (-emitter drive) voltage	Applied across G1-Es1/G2-Es2 terminals	13.5	15.0	16.5	V
R_G	External gate resistance	Per switch	1.0	-	10	Ω

CHIP LOCATION (Top view)

Dimension in mm, tolerance: ±1 mm



Tr1/Tr2: IGBT, Di1/Di2: FWD

TEST CIRCUIT AND WAVEFORMS





Switching characteristics test circuit and waveforms



t_{rr}, Q_{rr} characteristics test waveform



IGBT Turn-on switching energy



IGBT Turn-off switching energy



FWD Reverse recovery energy

Turn-on / Turn-off switching energy and Reverse recovery energy test waveforms (Integral time instruction drawing)

TEST CIRCUIT



Tr1



Tr2

V_{CEsat} characteristics test circuit



Di1



Di2

V_{EC} characteristics test circuit

PERFORMANCE CURVES

OUTPUT CHARACTERISTICS (TYPICAL)



COLLECTOR-EMITTER SATURATION VOLTAGE CHARACTERISTICS (TYPICAL)



COLLECTOR-EMITTER VOLTAGE CHARACTERISTICS (TYPICAL)



FREE WHEELING DIODE FORWARD CHARACTERISTICS (TYPICAL)



PERFORMANCE CURVES

HALF-BRIDGE SWITCHING CHARACTERISTICS (TYPICAL)

V_{CC}=600 V, V_{GE}=±15 V, R_G=1.0 Ω, INDUCTIVE LOAD
————: T_{vj}=150 °C, - - - - -: T_{vj}=125 °C



HALF-BRIDGE SWITCHING CHARACTERISTICS (TYPICAL)

V_{CC}=600 V, V_{GE}=±15 V, I_C=600 A, INDUCTIVE LOAD
————: T_{vj}=150 °C, - - - - -: T_{vj}=125 °C



HALF-BRIDGE SWITCHING CHARACTERISTICS (TYPICAL)

V_{CC}=600 V, V_{GE}=±15 V, R_G=1.0 Ω, INDUCTIVE LOAD
————: T_{vj}=150 °C, - - - - -: T_{vj}=125 °C



HALF-BRIDGE SWITCHING CHARACTERISTICS (TYPICAL)

V_{CC}=600 V, V_{GE}=±15 V, I_C=600 A, INDUCTIVE LOAD
————: T_{vj}=150 °C, - - - - -: T_{vj}=125 °C



PERFORMANCE CURVES

CAPACITANCE CHARACTERISTICS (TYPICAL)



FREE WHEELING DIODE REVERSE RECOVERY CHARACTERISTICS (TYPICAL)



GATE CHARGE CHARACTERISTICS (TYPICAL)



TRANSIENT THERMAL IMPEDANCE CHARACTERISTICS (MAXIMUM)



i	1	2	3	4
Ri [K/kW]	1.036E-02	7.891E-02	6.654E-01	2.453E-01
τi (s)	1.177E-05	4.442E-04	8.189E-03	2.428E-02

PERFORMANCE CURVES

TURN-OFF SWITCHING SAFE OPERATING AREA (REVERSE BIAS SAFE OPERATING AREA) (MAXIMUM)

V_{CC}≤850 V, V_{GE}=±15 V, R_G=1.0~10 Ω,
————: T_{vj}=25~150 °C (Normal load operations (Continuous)
- - - - - -: T_{vj}=175 °C (Unusual load operations (Limited period)



SHORT-CIRCUIT SAFE OPERATING AREA (MAXIMUM)

V_{CC}≤800 V, V_{GE}=±15 V, R_G=1.0~10 Ω,
T_{vj}= 25 ~ 150 °C, t_W≤8 μs, Non-Repetitive



Note: The characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.

Important Notice

The information contained in this datasheet shall in no event be regarded as a guarantee of conditions or characteristics. This product has to be used within its specified maximum ratings, and is subject to customer's compliance with any applicable legal requirement, norms and standards.

Except as otherwise explicitly approved by Mitsubishi Electric Corporation in a written document signed by authorized representatives of Mitsubishi Electric Corporation, our products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

In usage of power semiconductor, there is always the possibility that trouble may occur with them by the reliability lifetime such as Power Cycle, Thermal Cycle or others, or when used under special circumstances (e.g. condensation, high humidity, dusty, salty, highlands, environment with lots of organic matter / corrosive gas / explosive gas, or situations which terminals of semiconductor products receive strong mechanical stress). Therefore, please pay sufficient attention to such circumstances. Further, depending on the technical requirements, our semiconductor products may contain environmental regulation substances, etc. If there is necessity of detailed confirmation, please contact our nearest sales branch or distributor.

The contents or data contained in this datasheet are exclusively intended for technically trained staff. Customer's technical departments should take responsibility to evaluate the suitability of Mitsubishi Electric Corporation product for the intended application and the completeness of the product data with respect to such application. In the customer's research and development, please evaluate it not only with a single semiconductor product but also in the entire system, and judge whether it's applicable. As required, pay close attention to the safety design by installing appropriate fuse or circuit breaker between a power supply and semiconductor products to prevent secondary damage. Please also pay attention to the application note and the related technical information.

Keep safety first in your circuit designs!

Mitsubishi Electric Corporation puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of non-flammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

- These materials are intended as a reference to assist our customers in the selection of the Mitsubishi Electric Semiconductor product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Mitsubishi Electric Corporation or a third party.
- Mitsubishi Electric Corporation assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
- All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Mitsubishi Electric Corporation without notice due to product improvements or other reasons. It is therefore recommended that customers contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor for the latest product information before purchasing a product listed herein.
  The information described here may contain technical inaccuracies or typographical errors. Mitsubishi Electric Corporation assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
  Please also pay attention to information published by Mitsubishi Electric Corporation by various means, including the Mitsubishi Electric Semiconductor home page (https://www.MitsubishiElectric.com/semiconductors/).
- When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Mitsubishi Electric Corporation assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
- Mitsubishi Electric Corporation semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
- The prior written approval of Mitsubishi Electric Corporation is necessary to reprint or reproduce in whole or in part these materials.
- If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
  Any diversion or re-export contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
- Please contact Mitsubishi Electric Corporation or an authorized Mitsubishi Electric Semiconductor product distributor for further details on these materials or the products contained therein.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mitsubishi Electric:

CM600DY-24T