

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190030140](#)
Status: **Active**
Overview: [Standard Quick-Disconnect Terminals](#)
Description: InsulKrimp Quick Disconnect, Female, Continuous Molded Strip, Tab 4.75 x 0.51mm

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-19902-011-001 \(PDF\)](#)
[Product Specification PS-19902-008-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)


General
Product Family Quick Disconnects
Series [19003](#)
Comments Funnel Entry
Crimp Quality Equipment Yes
Insulated Fully
Overview [Standard Quick-Disconnect Terminals](#)
Product Name InsulKrimp
Type Quick Disconnect
UPC 800756386980

Physical
Barrel Type Closed
Color - Resin Yellow
Gender Female
Glow-Wire Capable No
Insulation Nylon (PA)
Lock to Mating Part None
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Nylon
Net Weight 0.751/g
Orientation Straight
Packaging Type Reel
Plating min - Mating 4.064µm
Plating min - Termination 4.064µm
Polarized to Mating Part No
Tab Thickness 0.51mm
Tab Width 4.75mm
Temperature Range - Operating -65° to +105°C
Termination Interface: Style Crimp or Compression
Wire Size AWG 24, 26

Electrical
Voltage - Maximum 600V

Material Info
Engineering Number M-2210VC

Reference - Drawing Numbers
Product Specification PS-19902-008-001, PS-19902-011-001
Sales Drawing SD-19003-003-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)
1,2-
Benzenedicarboxylic
acid, bis(3-
methylbutyl)
1,2-diethoxyethane
Dibutyltin-dichloride
1,3-Propanesultone
C.I. Direct Black 38
Disodium-octaborate
2-ethylhexyl 10-
ethyl-4,4-dioctyl-7-
oxo-8-oxa-3,
2-(2H-Benzotriazol-2-
yl)-4,6-
ditertpentylphenol
2-(2H-Benzotriazol-2-
yl)-4-(tert-butyl)-6-
(sec-b
Terphenyl,
hydrogenated
1,2-
Benzenedicarboxylic
acid, dihexyl ester,
bra
diisohexyl phthalate
1,2-
Benzenedicarboxylic
acid, dipentyl ester, br
n-pentyl-
isopentylphthalate
Boric acid
Aluminosilicate
Refractory Ceramic
Fibres
Zirconia
Aluminosilicate

China RoHS

Refractory Ceramic
Fibr
Tris(4-nonylphenyl,
branched and linear)
phosphi
Pyrene
Diocetyl tin dilaurate,
stannane, dioctyl-,
bis(co
Perfluorononan-1-
oic acid
(2,2,3,3,4,4,5,5,6,6,7
reaction mass of
2-ethylhexyl 10-
ethyl-4,4-dioct
Perfluorohexane-1-
sulphonic acid and its
salts
Strontium-chromate
1,2-
Benzenedicarboxylic
acid, di-C7-11-
branched
Diboron-trioxide
Cadmium-oxide
Cadmium-sulphide
Lead(II,IV)-oxide
Pentalead-tetraoxide-
sulphate
Trilead-dioxide-
phosphonate
Cyanamide, lead(2+)
salt (1:1)
Cadmium Hydroxide
Sulfurous Acid, Lead
Salt, Dibasic
4-aminoazobenzene
Dicyclohexyl-
phthalate
Dihexyl-phthalate
Phenanthrene
Imidazolidine-2-thione
Dipentyl phthalate
Benzo(ghi)perylene
Octanoic acid,
2,2,3,3,4,4,5,5,6,6,7,7,8,8,8-
pen
Dodecamethylcyclhexasiloxane
Decamethylcyclopentasiloxane
Octamethylcyclotetrasiloxane
Disodium 3,3'-[[1,1'-
Biphenyl]-4,4'-
Diylbis(Azo)

Halogen-Free
Status
Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[19003](#) Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Mini-Mac Applicator	638830600

This document was generated on 09/13/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19003-0140](#)