

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0010112043](#)  
**Status:** **Active**  
**Overview:** [KK® Interconnect System - Molex](#)  
**Description:** [KK 254 Crimp Housing, High Pressure, 4 Circuits, Natural](#)

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification PS-7879-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Drawing (PDF)</a>	

**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	Crimp Housings
Series	<a href="#">7880</a>
Application	Signal, Wire-to-Board
Overview	<a href="#">KK® Interconnect System - Molex</a>
Product Name	KK 254
UPC	800753612297

**Physical**

Circuits (maximum)	4
Color - Resin	Natural (White)
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	0.392/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Stackable	No
Temperature Range - Operating	See Product Specification

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

Engineering Number	7880-4B
--------------------	---------

**Reference - Drawing Numbers**

Product Specification	PS-7879-001
Sales Drawing	SD-7880



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[7880 Series](#)

**Mates With**

KK254 PCB Headers [42375](#) , [42377](#) , [42376](#)  
, [4030](#) , [6373](#) , [6410](#)

**Use With**

[7879](#) KK High Pressure Crimp Terminal

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[10-11-2043](#)