

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190440138

Status:

Active

Overview:

High-Temperature Temp Terms Terminals and Splices

Description:

Krimptite Ring Tongue Terminal for 14-16 Heavy Duty AWG Wire

Documents:

Drawing (PDF)

3D Model (PDF)

3D Model

Product Specification PS-19902-011-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19044
Comments	Heavy Duty
Crimp Quality Equipment	Yes
Overview	High-Temperature Temp Terms Terminals and Splices
Product Name	Krimptite
Type	Ring
UPC	800753050822
Physical	
Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	3.189/g
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	1/2" (M12)
Termination Interface: Style	Crimp or Compression
Wire Size AWG	14, 16
Wire Size mm²	1.30-2.00
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	B-101-12HDT
Reference - Drawing Numbers	
Product Specification	PS-19902-011-001
Sales Drawing	SD-19044-008-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

Green Image

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Low-Halogen

Status

For more information, please visit Contact US

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19044 Series

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
Perishable Tooling	190270135
Spacers for tape product	
ATP Perishable	190270301
Tool Kit used in ATP	
Presses that Process	
Product on Tape	

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

19044-0138