

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190670026

Status:


Active

Overview:

Solderless Terminals

Description:

NylaKrimp Funnel Entry Ring Tongue Terminal for 8 AWG Wire, Stud Size 5/16" (M8)



Documents:	
3D Model	Product Specification PS-19902-015-001 (PDF)
Drawing (PDF)	Product Specification PS-19902-016-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-19902-011-001 (PDF)	
Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19067
Comments	Type II Insulated; Class 2
Crimp Quality Equipment	Yes
Overview	Solderless Terminals
Product Name	NylaKrimp
Type	Ring
UPC	800753065598
Physical	
Barrel Type	Closed - Brazed
Flammability	94V-2
Insulation	Nylon (PA)
Material - Plating Mating	Tin
Net Weight	4.149/g
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	5/16" (M8)
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	8.98mm max.
Wire Size AWG	8
Material Info	
Engineering Number	D-951-56T
Reference - Drawing Numbers	
Product Specification	PS-19902-011-001, PS-19902-015-001, PS-19902-016-001
Sales Drawing	SD-19067-017-001

EU ELV
Not Relevant

EU RoHS
Compliant
REACH SVHC
Contained Per -
D(2021)4569-DC (8
July 2021)
Tris(2-chloroethyl)
phosphate
Boric acid, disodium
salt, hydrate
Silicic acid (H2Si2O5),
barium salt (1:1),
lead-
Phenanthrene
Dodecamethylcyclhexasiloxane
2,4-Di-tert-butyl-6-(5-
chlorobenzotriazol-2-
yl)p
diisohexyl phthalate
Boric acid
Fluoranthene
Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]o
Dioctyltin dilaurate,
stannane, dioctyl-,
bis(co
Halogen-Free
Status
Low-Halogen
For more information, please visit [Contact US](#)

China RoHS

Green Image
Not Relevant
Not Contained

Search Parts in this Series
19067 Series

Application Tooling | **FAQ**
Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Crimp Dies for 8 AWG Insulkrimp and NylaKrimp Mylar Tape, use with the 640162000 Tape Crimp Module and 638017600 TM-4000 Crimp Press	<u>190472030</u>
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>192880220</u>

This document was generated on 08/26/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19067-0026](#)