

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191180080

Status:

Active

Overview:

Solderless Terminals

Description:

Krimptite Flanged Spade Tongue Terminal for 10-12 AWG Wire, Stud Size 8 (M4), Length 19.91mm

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-013-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR18689

E32244

General

Product Family

Series

Crimp Quality Equipment

Overview

Product Name

Type

UPC

Ring and Spade Terminals

19118

Yes

Solderless Terminals

Krimptite

Spade

800755082784

Physical

Barrel Type

Insulation

Material - Plating Mating

Net Weight

Packaging Type

Stud Size

Wire Size AWG

Wire Size mm²

Closed

None

Tin

1.447/g

Bag

8 (M4)

10, 12

4.00-6.00

Material Info

Engineering Number

C-1104-08


Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-19902-011-001, PS-19902-013-001

CCD10401-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

Green Image

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Low-Halogen

Status

For more information, please visit Contact US

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19118 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm² - 0.5mm²	640030100
Crimp Head for the AT-200 Pneumatic Hand Tool	640070100
ServiceGrade Hand Crimp Tool - Ratchet	640160038

This document was generated on 08/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19118-0080](#)