

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192110002](#)
Status: **Active**
Overview: [Wire Pins](#)
Description: Krimptite Wire Pin Terminal for 12-10 AWG Wire, Mylar Tape Carrier

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-19902-015-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
UL E32244

General

Product Family Crimp Terminals
Series [19211](#)
Application Power, Wire-to-Component
Comments Pin Length 11.43mm
Crimp Quality Equipment Yes
Overview [Wire Pins](#)
Packaging Alternative [192110001](#) (Loose)
Product Name Wire Pin
UPC 800753053205

Physical


Gender Male
Material - Metal Copper
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 1.465/g
Packaging Type Adhesive Tape on Reel
Plating min - Mating 0.762µm
Plating min - Termination 0.762µm
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 3.45mm max.
Wire Size AWG 10, 12
Wire Size mm² N/A

Material Info

Engineering Number WP-1210T

Reference - Drawing Numbers

Product Specification PS-19902-011-001, PS-19902-015-001
Sales Drawing SD-19211-002-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[19211](#) Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	190270088
Mini-Mac Applicator	638851000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19211-0002](#)