

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:	<u>0011184997</u>
Status:	Active
Overview:	Application Tooling
Description:	Conductor Anvil

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

General	
Product Family	Application Tooling
Series	<u>207126</u>
Comments	See Tooling Specification (PDF) Above
Function	Cutter
Geographic Area	Global
Level of Automation	Semi-Automatic
More Detailed Tech Information	<u>applicationtooling@molex.com</u>
Overview	<u>Application Tooling</u>
Product Name	N/A
Tool Type	Applicator
UPC	800753900738
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight	7.000/g
------------	---------

Material Info

Engineering Number 60816A107

Reference - Drawing Numbers

Application Tooling Documents



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207126 Series

Use With

11182191, 11182193, 11182194,
11183140, 11183184, Li nk:11183187,
638933000, 638933070, 638933100,
638933170, 638933200, 638933270,
638933300, 638933370

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[11-18-4997](#)