

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION


Part Number: [0192900001](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Die Set (large) for the HHLS Hydraulic Crimper

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Application Tooling
Series [207122](#)
Function Crimp
Geographic Area Global
Level of Automation Manual
More Detailed Tech Information applicationtooling@molex.com
Overview [Application Tooling](#)
Product Name ETC
Tool Type Crimp Module
UPC 800753111738
Warranty Disclaimer CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info
Engineering Number HHL-D-110

Reference - Drawing Numbers
Application Tooling Documents
ATS-192900001-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001



Series image - Reference only

EU ELV
Not Reviewed

EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
---	-------------------

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[207122 Series](#)

Use With
Molex HHLS Air Powered Hydraulic Crimper 12 Ton [192860058](#) , Manual Putt Pump Hydraulic System [192860117](#) , Electric Powered Hydraulic System [192861300](#)

Application Tooling Description	FAQ Product #
VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Stud Size 6 (M3.5)	191930143
VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Stud Size 8 (M4)	191930146
VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Stud Size 10 (M5)	191930149
VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Stud Size 1/4" (M6)	191930152

VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Stud Size 5/16" (M8)	<u>191930157</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930159</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930163</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930167</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930171</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930179</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930184</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930186</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930187</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930192</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930195</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930198</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930200</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930202</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930204</u>
VersaKrimp Parallel Splice for 8 AWG Wire	<u>192050004</u>
VersaKrimp Butt Splice for 8 AWG Wire	<u>192150034</u>
Step Down Butt Splice for 8-12 AWG Wire	<u>192150037</u>
Compression Style Ring Tongue Terminal for 8 AWG Wire, Stud Size 10 (M5), Plated,	<u>192210223</u>
Compression Style Ring Tongue Terminal for 8 AWG Wire, Stud Size 1/4" (M6), Plated	<u>192210224</u>

	Compression	<u>192210225</u>
	Style Ring Tongue	
	Terminal for 8 AWG	
	Wire, Stud Size	
	5/16" (M8), Plated	
	Compression	<u>192210226</u>
	Style Ring Tongue	
	Terminal for 8 AWG	
	Wire, Stud Size	
	3/8" (M9), Plated,	
	Wide Pad	
	Compression	<u>192210408</u>
	Style Ring tongue	
	Terminal for 8 AWG	
	Wire, Stud Size	
	(M5), Unplated	
	Compression	<u>192210409</u>
	Style Ring Tongue	
	Terminal for 8 AWG	
	Wire, Stud Size	
	1/4" (M6), Unplated	
	Compression	<u>192210410</u>
	Style Ring Tongue	
	Terminal for 8 AWG	
	Wire, Stud Size	
	3/8" (M9), Unplated,	
	Wide Pad	
	Compression	<u>192210411</u>
	Style Ring Tongue	
	Terminal for 8 AWG	
	Wire, Stud Size	
	5/16" (M8), Unplated	
	Compression	<u>192210414</u>
	Style Ring Tongue	
	Terminal for 8 AWG	
	Wire, Stud Size	
	1/2" (M12), Plated,	
	Extra Wide Pad	
	Compression	<u>192210415</u>
	Style Ring Tongue	
	Terminal for 8 AWG	
	Wire, Stud Size	
	1/2" (M12), Unplated,	
	Extra Wide Pad	
	Compression	<u>192210481</u>
	Style Ring Tongue	
	Terminal for 8 AWG	
	Wire, Stud Size	
	3/8" (M9), Unplated,	
	Extra Wide Pad	
	Compression	<u>192210482</u>
	Style Ring Tongue	
	Terminal for 8 AWG	
	Wire, Stud Size	
	5/16" (M8), Unplated,	
	Wide Pad	
	Compression	<u>192210483</u>
	Style Ring Tongue	
	Terminal for 8 AWG	
	Wire, Stud Size	
	5/16" (M8), Plated,	
	Wide Pad	
	Compression	<u>192210484</u>
	Style Ring Tongue	
	Terminal for 8 AWG	

Wire, Stud Size
3/8" (M9), Plated,
Extra Wide Pad
Compression 192210562
Style Ring Tongue
Terminal for 8 AWG
Wire, Stud Size Style
1/4", Unplated, Wide
Pad
Compression 192210563
Style Ring Tongue
Terminal for 8 AWG
Wire, Stud Size
1/4" (M6), Plated,
Wide Pad

This document was generated on 07/30/2021
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19290-0001](#)