


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0194350812](#)
Status: **Active**
Overview: [MX150L Industrial Sealed Connector System](#)
Description: MX150L 8 Circuit Rear Mount Flange Plug for 18-22 AWG Wire, with Gasket, Black

Documents:
[3D Model](#) [Packaging Specification PK-19435-001-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [Brochure \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19417-001-001 \(PDF\)](#)

Agency Certification	
UL	E152602
General	
Product Family	Crimp Housings
Series	19435
Application	Power, Wire-to-Wire
Comments	Mat Seal Color is Red. IP67 rated; conforms to UL 1977. NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec (TCS)
Overview	MX150L Industrial Sealed Connector System
Product Name	MX150L
UPC	822350301039
Physical	
Circuits (maximum)	8
Color - Resin	Black
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Lock to Mating Part	Yes
Net Weight	23.990/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	5.84mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C
Electrical	
Current - Maximum per Contact	18.0A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-19435-001-001
Product Specification	PS-19417-001-001
Sales Drawing	SD-19435-008-001



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Not Reviewed REACH SVHC Not Contained Per - ED/108/2014 (17 Dec 2014) Halogen-Free Status Low-Halogen For more information, please visit Contact US	China RoHS
China ROHS ELV RoHS Phthalates	Green Image Not Relevant Not Reviewed

Search Parts in this Series
[19435](#) Series

Mates With
[19418](#) Receptacle Assemblies

Use With
[19417](#) Male Crimp Terminals

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19435-0812](#)