

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0313874017](#)
Status: **Active**
Overview: [MX123 Sealed Connection System](#)
Description: 2.54mm Pitch, MX123 Header, 80 Circuits Shrouded Assembly, Qty(80) 0.64mm Square Signal Pins, Harness Side Key Code G, Blue (Ag Mate Side Finish)

Documents:

3D Model	Application Specification AS-31386-200-001 (PDF)
Drawing (PDF)	Packaging Specification PK-31301-916-001 (PDF)
3D Model (PDF)	Test Summary TS-31387-1658-001 (PDF)
Product Specification PS-31387-200-001 (PDF)	Datasheet (PDF)
Product Specification PS-34566-0000-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	PCB Headers
Series	31387
Application	Automotive, Power, Wire-to-Board
Overview	MX123 Sealed Connection System
Product Name	MX123
UPC	883906178659

Physical

Breakaway	No
Circuits (Loaded)	80
Circuits (maximum)	80
Color - Resin	Blue
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Plating Mating	Silver
Material - Plating Termination	Tin
Net Weight	23.585/g
Number of Rows	4
Orientation	Vertical
PC Tail Length	6.50mm
PCB Locator	No
PCB Retention	None
Packaging Type	Carton
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +125°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	11.0A
Voltage - Maximum	500V

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

[31387 Series](#)

Mates With

[MX123 Female Harness Connector Assembly 34566](#)

Use With

[34736 MX64 Female Terminals Ag](#)

Reference - Drawing Numbers

Application Specification	AS-31386-200-001
Packaging Specification	PK-31301-916-001
Product Specification	PS-31387-200-001, PS-34566-0000-001
Sales Drawing	SD-31387-080-000, SD-31387-173-000
Test Summary	TS-31387-1658-001

This document was generated on 10/06/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[31387-4017](#)