

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [31408-1122](#)
Status: **Active**
Overview: [Stac64™ Single, Multi-Pocket and Hybrid Header System](#)
Description: [USCAR 2.54mm Pitch Receptacle, 12 Circuits, Polarization C, Brown](#)

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-31408-100 \(PDF\)](#)
[Application Specification AS-34691-100 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family [Crimp Housings](#)
Series [31408](#)
Application [Power, Wire-to-Board](#)
Comments [Polarization C](#)
Overview [Stac64™ Single, Multi-Pocket and Hybrid Header System](#)


Product Name [USCAR](#)
UPC [822348633456](#)

Physical
Circuits (maximum) [12](#)
Circuits Detail [12](#)
Color - Resin [Brown](#)
Gender [Female](#)
Glow-Wire Compliant [No](#)
Keying to Mating Part [None](#)
Lock to Mating Part [No](#)
Material - Resin [Modified Polystyrene](#)
Net Weight [4.475/g](#)
Number of Rows [2](#)
Packaging Type [Carton](#)
Panel Mount [No](#)
Pitch - Mating Interface [2.54mm](#)
Polarized to Mating Part [Yes](#)
Ports [1](#)
Stackable [No](#)
Temperature Range - Operating [-40°C to +100°C](#)

Electrical
Current - Maximum per Contact [10.2A](#)

Material Info

Reference - Drawing Numbers
[Application Specification AS-34691-100](#)
[Product Specification PS-31408-100](#)
[Sales Drawing SD-31408-900](#)



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[31408Series](#)

Mates With
[34691 Stac64 Right Angle Assembly](#). [34690 Stac64 Vertical Assembly](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[31408-1202](#) [31408-1122](#)