

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0347082016

Status:

Active

Overview:

Stac64 Single, Multi-Pocket and Hybrid Header System

Description:

Stac64 2 Bay Right-Angle Headers, 32 Circuits, Bay A 12 Circuit Signal Header, Polarization B, Gray; Bay B 20 Circuit Signal Header, Polarization D, Green; Tray

Documents:

3D Model

3D Model (PDF)


Drawing (PDF)

Application Specification AS-34729-020-001 (PDF)

Packaging Specification PK-31300-892-001 (PDF)

Brochure (PDF)

RoHS Certificate of Compliance (PDF)



Series image - Reference only

General	
Product Family	PCB Headers
Series	34708
Application	Automotive, Power, Wire-to-Board
Comments	Bay A 12 Circuits Stac64 Right Angle Signal Header, Polarization B. Bay B 20 Circuits Stac64 Right Angle Signal Header, Polarization D
Overview	Stac64 Single, Multi-Pocket and Hybrid Header System
Product Name	Stac64
UPC	884982416642
Physical	
Breakaway	No
Circuits (Loaded)	32
Circuits (maximum)	32
Color - Resin	Gray, Green
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	14.839/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	3.36mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Packaging Type	Tray
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +100°C
Termination Interface: Style	Through Hole

Electrical

EU ELV Compliant	
EU RoHS Compliant	China RoHS
REACH SVHC Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free Status Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
34708 Series

Mates With
31408 USCAR 2.54mm (.100") Pitch Receptacle, 31372 5.25mm (.206") Pitch Hybrid Receptacle Assembly, 34729 2.54mm (.100") Pitch Stac64 Right Angle Receptacle

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	500V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	040
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-34729-020-001
Packaging Specification	PK-31300-892-001
Sales Drawing	SD-34708-200-001

This document was generated on 10/06/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34708-2016](#)