

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0015921050

Status:

Active

Overview:

EBBI 50D Connector System

Description:

1.27mm Pitch EBBI 50D Receptacle, Vertical, 50 Circuits, 3.40mm PC Tail Length

Documents:

3D Model (PDF)

3D Model


Drawing (PDF)

Product Specification PS-71660-001 (PDF)

Packaging Specification PK-71660-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
Application tooling part link	
Application Tooling Part Link	62200-4600
Application Tooling Part Link	62200-5500
General	
Product Family	PCB Receptacles
Series	71660
Application	Board-to-Board, Signal
Overview	EBBI 50D Connector System
Product Name	EBBI
UPC	800754314916
Physical	
Circuits (Loaded)	50
Circuits (maximum)	50
Color - Resin	Black
Durability (mating cycles max)	2000
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2.990/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.40mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
Packaging Type	Tray
Pitch - Mating Interface	1.27mm
Plating min - Mating	0.762µm
Plating min - Termination	0.254µm
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	1.0A
Voltage - Maximum	30V
Solder Process Data	



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

71660 Series

Mates With

71661

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
IDT - Manual Press	622004600
IDT - Manual Press	622005500

Lead-free	Process Capability	SMC&WAVE
	Process Temperature max. C	260
Material Info		
	Engineering Number	A-71660-1050
Reference - Drawing Numbers		
	Packaging Specification	PK-71660-001
	Product Specification	PS-71660-001
	Sales Drawing	SDA-71660-1XXX-001

This document was generated on 09/23/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15-92-1050](#)