

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION


Part Number: 0015921450
Status: Active
Overview: EBBI 50D Connector System
Description: 1.27mm Pitch EBBI 50D Receptacle, Vertical, 50 Circuits, 2.79mm PC Tail Length

Documents:	
3D Model	Product Specification PS-71660 (PDF)
3D Model (PDF)	Product Specification PS-71660-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
Application tooling part link	
Application Tooling Part Link	62200-4600
Application Tooling Part Link	62200-5500
General	
Product Family	PCB Receptacles
Series	71660
Application	Board-to-Board, Signal
Overview	EBBI 50D Connector System
Product Name	EBBI
UPC	800754397421
Physical	
Circuits (Loaded)	50
Circuits (maximum)	50
Color - Resin	Black
Durability (mating cycles max)	2000
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2.990/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	2.79mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
Packaging Type	Tray
Pitch - Mating Interface	1.27mm
Plating min - Mating	0.762µm
Plating min - Termination	0.254µm
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

Electrical	
Current - Maximum per Contact	1.0A
Voltage - Maximum	30V

Solder Process Data



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)4578-DC (25 June 2020)	
Halogen-Free Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
71660 Series

Mates With
71661

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
IDT - Manual Press	622004600
IDT - Manual Press	622005500

Lead-free	Process Capability	SMC&WAVE
Process Temperature max.	C	260
Material Info		
Engineering Number		A716601350
Reference - Drawing Numbers		
Product Specification		PS-71660, PS-71660-001
Sales Drawing		SDA-71660-1XXX-001

This document was generated on 01/11/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

15-92-1450