

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0022124112](#)
Status: **Active**
Overview: [KK Interconnect Solutions](#)
Description: KK 254 Wire-to-Board Header, Right-Angle, with Friction Lock, 11 Circuits

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-99020-0088-001 \(PDF\)](#)
[Packaging Specification PK-7478-001-000 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family PCB Headers
Series [7395](#)
Application Signal, Wire-to-Board
Overview [KK Interconnect Solutions](#)
Product Name KK 254
UPC 800753728400

Physical

Breakaway No
Circuits (Loaded) 11
Circuits (maximum) 11
Color - Resin Natural (White)
Durability (mating cycles max) 100
First Mate / Last Break No
Flammability 94V-0
Glow-Wire Capable No
Guide to Mating Part No
Keying to Mating Part None
Lock to Mating Part Yes
Material - Metal Brass
Material - Plating Mating Gold
Material - Plating Termination Tin
Material - Resin Nylon
Net Weight 1.299/g
Number of Rows 1
Orientation Right Angle
PC Tail Length 3.80mm
PCB Locator No
PCB Retention None
PCB Thickness - Recommended 1.60mm
Packaging Type Bag
Pitch - Mating Interface 2.54mm
Pitch - Termination Interface 2.54mm
Plating min - Mating 0.508µm
Plating min - Termination 0.508µm
Polarized to PCB Yes
Shrouded Partial
Stackable No
Temperature Range - Operating See Product Specification
Termination Interface: Style Through Hole

Electrical



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series

[7395](#) Series

Mates With

[2695](#) KK Crimp Terminal Housing, [6471](#)
KK Crimp Terminal Housing, [7720](#) KK IDT
Double Cantilever

Current - Maximum per Contact	4.0A
Voltage - Maximum	500V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235
Material Info	
Engineering Number	739511BG
Reference - Drawing Numbers	
Packaging Specification	PK-7478-001-000
Product Specification	PS-99020-0088-001
Sales Drawing	SD-7395-001-001

This document was generated on 12/28/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

22-12-4112