

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0348259125

Status:

Active

Overview:

Mini50 Connection Systems

Description:

Mini50 Unsealed Vertical Header, Dual Row, 12 Circuit, Polarization Option B, Gray, Tube



Series image - Reference only

Documents:

- [3D Model](#)
- [3D Model \(PDF\)](#)
- [Drawing \(PDF\)](#)
- [Product Specification PS-34791-020-001 \(PDF\)](#)
- [Application Specification AS-34791-020-001 \(PDF\)](#)
- [Application Specification AS-34791-020-CH-001 \(PDF\)](#)
- [Application Specification AS-34791-020-FR-001 \(PDF\)](#)
- [Packaging Specification PK-31301-688-001 \(PDF\)](#)
- [Test Summary 347910020-TS-000 \(PDF\)](#)
- [Datasheet \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	PCB Headers
Series	34825
Application	Automotive, Power, Signal, Wire-to-Board
Overview	Mini50 Connection Systems
Product Name	Mini50
UPC	887191338705

Physical

Breakaway	No
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Gray
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2.200/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	2.87mm
PCB Locator	Yes
Packaging Type	Tube
Pitch - Mating Interface	2.00mm
Plating min - Mating	2.500µm
Plating min - Termination	2.500µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	4.0A (for reference only)
Voltage - Maximum	14V (typical operating)

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

34825 Series

Mates With

34824 Mini50 Unsealed Dual Row Receptacle

Material Info

Reference - Drawing Numbers

Application Specification	AS-34791-020-001, AS-34791-020-CH-001, AS-34791-020-FR-001
Packaging Specification	PK-31301-688-001
Product Specification	PS-34791-020-001
Sales Drawing	SD-34825-001-001
Test Summary	347910020-TS-000

This document was generated on 08/03/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34825-9125](#)