

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0348260160](#)  
**Status:** **Active**  
**Overview:** [Mini50 Connection Systems](#)  
**Description:** Mini50 Unsealed Right-Angle Header, Dual Row, 16 Circuit, Polarization Option A, 2.80mm Pin Length, Black, Tray

**Documents:**

<a href="#">3D Model (PDF)</a>	<a href="#">Application Specification AS-34791-020-FR-001 (PDF)</a>
<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-31301-440-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Test Summary 347910020-TS-000 (PDF)</a>
<a href="#">Product Specification PS-34791-020-001 (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Application Specification AS-34791-020-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification AS-34791-020-CH-001 (PDF)</a>	

**General**

Product Family	PCB Headers
Series	<a href="#">34826</a>
Application	Automotive, Power, Signal, Wire-to-Board
Overview	<a href="#">Mini50 Connection Systems</a>
Product Name	Mini50
UPC	887191338934

**Physical**


Breakaway	No
Circuits (Loaded)	16
Circuits (maximum)	16
Color - Resin	Black
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2.840/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	2.80mm
PCB Locator	Yes
Packaging Type	Tray
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

**Electrical**

Current - Maximum per Contact	4.0A (for reference only)
Voltage - Maximum	14V (typical operating)

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

[34826 Series](#)

**Mates With**

[Mini50 Unsealed Dual Row Receptacle 34824](#)

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-34791-020-001, AS-34791-020-CH-001, AS-34791-020-FR-001
Packaging Specification	PK-31301-440-001
Product Specification	PS-34791-020-001
Sales Drawing	SD-34826-001-001
Test Summary	347910020-TS-000

This document was generated on 02/01/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34826-0160](#)