

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0386006603

Status:


Active

Overview:

Beau Barrier Strips

Description:

6.35mm Pitch Beau PCB Tri-Barrier Terminal Strip, without Mounting Ends, 300V, 3 Circuits



Documents:	
3D Model	3D Model (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Terminal Blocks
Series	38600
Application	N/A
Component Type	One Piece
Overview	Beau Barrier Strips
Product Name	Fixed Mount Barrier
Type	Barrier Strip
UPC	800756242606
Physical	
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Black
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester Alloy
Number of Rows	1
Orientation	Horizontal
PC Tail Length	5.10mm
PCB Thickness - Recommended	3.18mm
Panel Mount	No
Pitch - Mating Interface	6.35mm
Pitch - Termination Interface	6.35mm
Polarized to Mating Part	No
Shrouded	Tri-Barrier
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +130°C
Wire Size AWG	18, 20, 22
Electrical	
Current - Maximum per Contact	10.0A
Voltage - Maximum	300V
Material Info	
Engineering Number	60503-C
Reference - Drawing Numbers	
Sales Drawing	SD-38600-001

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Contained Per -
D(2020)4578-DC (25
June 2020)
henicosafluoroundecanoic
acid
disodium 4-
amino-3-[[4'-[(2,4-
diaminophenyl)azo]
chromium trioxide
1,3-propanesultone
1-vinylimidazole
4,4'-methylenedi-o-
toluidine
dibutyltin dichloride
methoxyacetic acid
1,2-
Benzenedicarboxylic
acid, bis(3-
methylbutyl)
disodium 3,3'-[[1,1'-
biphenyl]-4,4'-
diylbis(azo)
octamethylcyclotetrasiloxane
benzene-1,2,4-
tricarboxylic acid 1,2-
anhydride
decamethylcyclopentasiloxane
dodecamethylcyclohexasiloxane
heptacosafuorotetradecanoic
acid
tricosafuorododecanoic
acid
Dipentyl phthalate
6-methoxy-m-toluidine
furan
1-bromopropane
nitrobenzene
4-o-tolylazo-o-
toluidine

ethylene thiourea
4-methyl-m-phenylenediamine
o-toluidine
butyl 4-hydroxybenzoate
dinoseb (ISO)
dihexyl phthalate (DnHP)
dicyclohexyl phthalate
N-methylacetamide
dimethyl sulphate
diethyl sulphate
4-aminoazobenzene
Fatty acids, C16-18, lead salts
[phthalato(2-)]dioxotrilead
Silicic acid (H₂Si₂O₅), barium salt (1:1), lead-
Perfluorohexane-1-sulphonic acid and its salts
5-sec-butyl-2-(2,4-dimethylcyclohex-3-en-1-yl)-5
1,2-benzenedicarboxylic acid, di-C6-10-alkyl est
Cadmium sulphate
Sodium perborate; perboric acid, sodium salt
hexahydro-2-benzofuran-1,3-dione
4-(1,1,3,3-tetramethylbutyl)phenol, ethoxylated
Perfluorononan-1-oic acid
(2,2,3,3,4,4,5,5,6,6,7
Reaction
products of 1,3,4-thiadiazolidine-2,5-d
Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]o
Chrysene
Cadmium nitrate
Pyrene
Tris(4-nonylphenyl, branched and linear)
phosphi
2,3,3,3-tetrafluoro-2-(heptafluoropropoxy)propio
4-(1,1,3,3-tetramethylbutyl)phenol, ethoxylated
Trixylyl phosphate
Zirconia
Aluminosilicate
Refractory Ceramic
Fibr
Aluminosilicate
Refractory Ceramic
Fibres

Boric acid
Disodium tetraborate
Hydrazine
1,3-BENZENEDIOL,
TRINITRO-, LEAD
SALT
n-pentyl-
isopentylphthalate
3-ethyl-2-methyl-2-
(3-methylbutyl)-1,3-
oxazolidi
1,2-
Benzenedicarboxylic
acid, dipentyl ester, br
pentacosafuorotridecanoic
acid
1,2-
Benzenedicarboxylic
acid, dihexyl ester,
bra
Terphenyl,
hydrogenated
2-(2H-benzotriazol-2-
yl)-4-(tert-butyl)-6-
(sec-b
2-(2H-benzotriazol-2-
yl)-4,6-
ditertpentylphenol
dibutylbis(pentane-2,4-
dionato-O,O')tin
2-ethylhexyl 10-
ethyl-4,4-dioctyl-7-
oxo-8-oxa-3,
Disodium-octaborate
sodium
peroxometaborate
Ammonium-
pentadecafluorooctanoate
pentazinc chromate
octahydroxide
1,2-dichloroethane
trilead diarsenate
2-methoxyaniline
arsenic acid
N,N-
dimethylacetamide
lead dipicrate
potassium
hydroxyoctaoxodizincatedichromate(1-)
bis(2-methoxyethyl)
ether
Calcium-arsenate
1,2-
Benzenedicarboxylic
acid, di-C6-8-
branched a
N-methyl-2-
pyrrolidone
1,2-
Benzenedicarboxylic
acid, di-C7-11-
branched
2-ethoxyethyl acetate
Cobalt sulphate

Acetic acid, cobalt(2+) salt
Carbonic acid, cobalt(2+) salt (1:1)
Boric acid, disodium salt, hydrate
sodium chromate
potassium dichromate
potassium chromate
ammonium dichromate
Tris(2-chloroethyl) phosphate
Lead sulfochromate yellow
Lead chromate molybdate sulfate red
lead chromate
Anthracene oil, anthracene-low; Anthracene Oil F
Anthracene oil, anthracene paste, distn. lights;
Anthracene oil, anthracene paste, anthracene fra
Anthracene oil, anthracene paste;
Anthracene Oil
Butylbenzylphthalate (BBP)
lead hydrogen arsenate
bis(2-ethylhexyl) phthalate (DEHP)
dibutyl phthalate (DBP)
4,4'-diaminodiphenylmethane
triethyl arsenate
Sulfurous acid, lead salt, dibasic
Acetic acid, lead salt, basic
cadmium hydroxide
Lead titanium zirconium oxide
dioxobis(stearato)trilead
tetralead trioxide sulphate
Trilead-dioxide-phosphonate
pentalead tetraoxide sulphate
lead oxide sulfate
Silicic acid, lead salt
cadmium chloride
lead dinitrate
pyrochlore, antimony
lead yellow
Cadmium-fluoride
cadmium
lead

α,α #Bis[4-(dimethylamino)phenyl]-4
(phenylamino)
[4-[[4-anilino-1-naphthyl][4-(dimethylamino)phen
1,3,5-
tris(oxiranylmethyl)-1,3,5-
triazine-2,4,6(
Lead oxide
trilead bis(carbonate)
dihydroxide
orange lead
cadmium sulphide
cadmium oxide (non-
pyrophoric)
Diboron-trioxide
bis(pentabromophenyl)
ether
4,4'-
bis(dimethylamino)-4''-
(methylamino)trityl
[4-[4,4'-
bis(dimethylamino)
benzhydrylidene]cycl
cadmium carbonate
1,2-dimethoxyethane
4,4'-
bis(dimethylamino)benzophenone
dichromium
tris(chromate)
phenolphthalein
lead diazide
1,2-
Benzenedicarboxylic
acid, bis(2-
methoxyethyl
Formaldehyde,
polymer with
benzenamine

**Halogen-Free
Status**

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[38600](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

38600-6603