

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0387068012

Status:

Active

Overview:

Beau Barrier Strips

Description:

8.26mm Pitch Beau PCB Terminal Strip, without Mounting Ends, Dual Level Terminal Block, 12 Circuits

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Component Type

Overview

Product Name

Type

UPC

Terminal Blocks

38706

N/A

One Piece

Beau Barrier Strips

Fixed Mount Barrier

Barrier Strip

883906405410

Physical

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Entry Angle

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Retention

PCB Thickness - Recommended

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Shrouded

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

Wire Size AWG

12

12

Black

N/A

None

Brass

Tin

Tin

Polysulfone

54.355/g

2

Vertical

3.56mm

None

1.57mm

No

8.26mm

8.26mm

N/A

Dual-Barrier

No

No

160°C

Through Hole

12, 14, 16, 18, 20, 22

Electrical

Current - Maximum per Contact

Voltage - Maximum

20.0A

300V

Material Info


Engineering Number

70D12-RC

Reference - Drawing Numbers

Sales Drawing

SD-38706-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

38706 Series

This document was generated on 08/17/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[38706-8012](#)