

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0387104705

Status:

Active

Overview:

Beau Barrier Strips

Description:

9.53mm Pitch Beau PCB Terminal Strip, Low Profile, Insulated PC Tail, 5 Circuits

Documents:

- 3D Model

Product Specification PS-38710-001-001 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)
- 3D Model (PDF)

General

Product Family

Terminal Blocks

Series

38710

Application

N/A

Component Type

One Piece

Overview

Beau Barrier Strips

Product Name

Fixed Mount Barrier

Type

Barrier Strip

UPC

800756283340

Physical

Circuits (Loaded)

5

Circuits (maximum)

5

Color - Resin

Black

Entry Angle

Horizontal

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

Polyester

Net Weight

41.000/g

Number of Rows

1

Orientation

Horizontal

PC Tail Length

5.30mm

PCB Retention

Yes

Panel Mount

No

Pitch - Mating Interface

9.53mm

Pitch - Termination Interface

9.53mm

Polarized to Mating Part

No

Shrouded

Dual-Barrier

Stackable

No

Surface Mount Compatible (SMC)

No

Temperature Range - Operating

-40° to +130°C

Termination Interface: Style

Screw or Lug

Wire Size AWG

14, 16, 18, 20, 22

Wire Size mm²

0.50-1.50

Electrical

Current - Maximum per Contact

15.0A

Voltage - Maximum

300V

Material Info

Engineering Number

71305

Reference - Drawing Numbers

Product Specification

PS-38710-001-001

Sales Drawing

SD-38710-006



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

China RoHS

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Relevant

Search Parts in this Series

38710 Series

Mates With

N/A

This document was generated on 07/28/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

38710-4705