

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0399300518

Status:

Active

Overview:

Eurostyle Terminal Blocks

Description:

3.81mm Pitch Beau EuroMate Pluggable PCB Terminal Block, Dual Level, 270° Wire Entry, with Retention Screws, 18 Circuits

Documents:

3D Model

RoHS Certificate of Compliance (PDF)

Drawing (PDF)

Agency Certification

UL

E48521

General

Product Family

Terminal Blocks

Series

39930

Application

N/A

Comments

with retention screws, with retention screws

Component Type

Plug

Overview

Eurostyle Terminal Blocks

Product Name

EuroMate Pluggable

Type

Euro Block

UPC

800756371634

Physical

Circuits (Loaded)

18

Color - Resin

Black

Entry Angle

Horizontal

Flammability

94V-0

Lock to Mating Part

Yes

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

Nylon

Number of Rows

2

Orientation

Vertical

PCB Retention

N/A

Panel Mount

No

Pitch - Mating Interface

3.81mm

Pitch - Termination Interface

3.81mm

Polarized to Mating Part

Yes

Shrouded

Tri-Barrier

Stackable

No

Temperature Range - Operating

105°C

Termination Interface: Style

Screw or Lug

Wire Size AWG

14, 16, 18, 20, 22

Wire Size mm²

0.50-1.50

Electrical

Current - Maximum per Contact

12.0A

Voltage - Maximum

300V

Material Info


Engineering Number

936918

Reference - Drawing Numbers

Sales Drawing

SD-39930-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per

-ED/01/2018 (15

January 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

39930 Series

Mates With

395151018 , 395161018

This document was generated on 09/21/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39930-0518](#)