

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0399400514

Status:

Active

Overview:

Eurostyle Terminal Blocks

Description:

5.08mm Pitch Beau EuroMate Pluggable PCB Terminal Block, Dual Level, 270° Wire Entry, with Retention Screws, 14 Circuits

Documents:

- 3D Model

Product Specification PS-39940-001-001 (PDF)
- 3D Model (PDF)

RoHS Certificate of Compliance (PDF)
- Drawing (PDF)

Agency Certification

UL

E48521

General

Product Family

Terminal Blocks

Series

39940

Application

N/A

Comments

Gold plating available

Component Type

Plug

Overview

Eurostyle Terminal Blocks

Product Name

EuroMate Pluggable

Type

Euro Block

UPC

800756373393

Physical

Circuits (Loaded)

14

Color - Resin

Black

Entry Angle

Horizontal

Flammability

94V-0

Lock to Mating Part

Yes

Material - Resin

Nylon

Number of Rows

2

Orientation

Vertical

PCB Retention

N/A

Panel Mount

No

Pitch - Mating Interface

5.08mm

Pitch - Termination Interface

5.08mm

Polarized to Mating Part

Yes

Shrouded

Tri-Barrier

Stackable

No

Temperature Range - Operating

130°C

Termination Interface: Style

Screw or Lug

Wire Size AWG

12, 14, 16, 18, 20, 22

Wire Size mm²

0.50-2.50

Electrical

Current - Maximum per Contact

15.0A

Voltage - Maximum

300V

Material Info

Engineering Number

946914


Reference - Drawing Numbers

Product Specification

PS-39940-001-001

Sales Drawing

SD-39940-003



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

39940 Series

Mates With

395350014 , 395354014 , 395360014 , 395364014

This document was generated on 07/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39940-0514](#)