

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0428206244

Status:

Active

Overview:

Mini-Fit Sr. Power Connectors

Description:

10.00mm Pitch Mini-Fit Sr. Header, Single Row, Right-Angle, 6.35mm PCB Thickness, Silver (Ag) Plating, 6 Circuits

Documents:

Drawing (PDF)

Product Specification PS-42815-001-001 (PDF)

Test Summary TS-42815-004-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Headers

Series

42820

Application

Power, Wire-to-Board

Overview

Mini-Fit Sr. Power Connectors

Product Name

Mini-Fit Sr.

UPC

889056247108

Physical

Breakaway

No

Circuits (Loaded)

6

Circuits (maximum)

6

Color - Resin

Black

Durability (mating cycles max)

30

First Mate / Last Break

No

Flammability

94V-0

Glow-Wire Capable

No

Guide to Mating Part

No

Keying to Mating Part

None

Lock to Mating Part

Yes

Material - Metal

Brass

Material - Plating Mating

Silver

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

19.454/g

Number of Rows

1

Orientation

Right Angle

PC Tail Length

8.30mm

PCB Locator

Yes

PCB Retention

Yes

PCB Thickness - Recommended

6.35mm

Packaging Type

Tube

Pitch - Mating Interface

10.00mm

Pitch - Termination Interface

10.00mm

Plating min - Mating

2.540µm

Plating min - Termination

2.540µm

Polarized to Mating Part

Yes

Polarized to PCB

Yes

Shrouded

Fully

Stackable

No

Surface Mount Compatible (SMC)


No

Temperature Range - Operating

-40° to +105°C

Termination Interface: Style

Through Hole



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

42820 Series

Mates With

Mini-Fit Sr. Receptacle Housing with TPA
42816

Electrical

Current - Maximum per Contact	50.0A
Voltage - Maximum	600V

Solder Process Data

Duration at Max. Process Temperature (seconds)	030
Lead-freeProcess Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	235

Material Info

Reference - Drawing Numbers

Product Specification	PS-42815-001-001
Sales Drawing	SDA-42820-0002-001
Test Summary	TS-42815-004-001

This document was generated on 10/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

42820-6244