

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0432238182

Status:

Active

Overview:

Magnetic and Modular Jacks/Plugs

Description:

Modular Jack, Right-Angle, Low Profile, 8/8, 8 Ports

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Packaging Specification PK-44150-004-000 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E107635

General

Product Family

Modular Jacks/Plugs

Series

43223

Comments

Flush Mount|Flangeless|External Shield

Component Type

PCB Jack

Magnetic

No

Overview

Magnetic and Modular Jacks/Plugs

Performance Category

3

Power over Ethernet (PoE)

N/A

Product Name

Modular Jack 8/8, RJ45

UPC

800754365833

Physical

Boot Color

N/A

Color - Resin

Black

Durability (mating cycles max)

500

Flammability

94V-0

Inverted / Top Latch

No

Jack Height

12.83mm

Lightpipes/LEDs

None

Material - Metal

Brass, Phosphor Bronze

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

32.657/g

Orientation

Right Angle (Side Entry)

PCB Locator

Yes

PCB Retention

Yes

PCB Thickness - Recommended

1.57mm

Packaging Type

Tray

Pitch - Mating Interface

1.02mm

Pitch - Termination Interface

1.27mm

Plating min - Mating

1.270µm

Plating min - Termination

2.540µm

Port Configuration

1x8

Positions / Loaded Contacts

8/8

Surface Mount Compatible (SMC)

No

Temperature Range - Operating

-40° to +85°C

Termination Interface: Style

Through Hole


Waterproof / Dustproof

No

Wire/Cable Type

N/A

Electrical



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

43223 Series

Mates With

FCC 68 Plugs

Current - Maximum per Contact	1.5A
Grounding to PCB	Yes
Shielded	Yes
Voltage - Maximum	150V AC (RMS)

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260

Material Info

Engineering Number	A432238182
--------------------	------------

Reference - Drawing Numbers

Packaging Specification	PK-44150-004-000
Sales Drawing	SDA-43223-001

This document was generated on 08/26/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

43223-8182