

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0026202101

Status:


Active

Overview:

[KK Interconnect Solutions](#)

Description:

KK 396 Wire-to-Board Header, Vertical Round Pin, 10 Circuits, Tin (Sn) Plating, with Mating Pin Length of 11.43mm (.450")



Series image - Reference only

Documents:

- [3D Model](#)
- [Drawing \(PDF\)](#)
- [3D Model \(PDF\)](#)
- [Product Specification PS-99020-0087-001 \(PDF\)](#)
- [Packaging Specification PK-3192-001-001 \(PDF\)](#)
- [Symbol Footprint Data SYM-26-20-2101 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Overview

Product Name

UPC

PCB Headers

3192

Board-to-Board, Power, Wire-to-Board

[KK Interconnect Solutions](#)

KK 396

800753734739

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Flammability

Glow-Wire Capable

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Polarized to PCB

Shrouded

Stackable

Temperature Range - Operating

Termination Interface: Style

No

10

10

Natural

25

No

94V-2

No

No

None

None

Brass

Tin

Tin

Nylon

2.430/g

1

Vertical

4.45mm

No

None

1.60mm

Bag

3.96mm

3.96mm

5.080µm

5.080µm

No

No

No

Yes

See Product Specification

Through Hole

EU ELV

Not Relevant

EU RoHS

Not Reviewed

China RoHS

REACH SVHC

Not Contained Per -
ED/39/2015 (15 June
2015)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

3192 Series

Mates With

3069 KK Crimp Terminal Housing, 3215 KK
396 PC Board Connector

Electrical

Current - Maximum per Contact	7.0A
Voltage - Maximum	250V

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235

Material Info

Engineering Number	319210A
--------------------	---------

Reference - Drawing Numbers

Packaging Specification	PK-3192-001-001
Product Specification	PS-99020-0087-001
Sales Drawing	SDAE-3192-NX
Symbol/Footprint Data	SYM-26-20-2101

This document was generated on 02/24/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[26-20-2101](#)