

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0026482112

Status:

Active

Overview:

KK Interconnect Solutions

Description:

KK 396 Breakaway Header, Right-Angle, 11 Circuits, Gold (Au) Plating

Documents:

- 3D Model

Packaging Specification PK-41662-001-001 (PDF)
- 3D Model (PDF)

Symbol Footprint Data SYM-26-48-1112-001 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-08-50-001 (PDF)

Agency Certification

CSA

LR19980

UL

E29179

Application tooling part link

Application Tooling Part Link

11-20-0901

General

Product Family

PCB Headers

Series

41662

Application

Board-to-Board, Power, Wire-to-Board

Overview

KK Interconnect Solutions

Product Name

KK 396

UPC

800754903424

Physical

Breakaway

Yes

Circuits (Loaded)

11

Circuits (maximum)

11

Color - Resin

Black

Durability (mating cycles max)

50

First Mate / Last Break

No

Flammability

94V-0

Glow-Wire Capable

No

Guide to Mating Part

No

Keying to Mating Part

None

Lock to Mating Part

None

Material - Plating Mating

Gold

Material - Plating Termination

Matte Tin

Net Weight

4.099/g

Number of Rows

1

Orientation

Right Angle

PC Tail Length

4.67mm

PCB Locator

No

PCB Retention

None

PCB Thickness - Recommended

1.60mm

Packaging Type

Bag

Pitch - Mating Interface

3.96mm

Pitch - Termination Interface

3.96mm

Polarized to Mating Part

Yes

Polarized to PCB

No

Shrouded

Partial

Stackable

No


Temperature Range - Operating

See Product Specification

Termination Interface: Style

Through Hole

Electrical



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[41662](#) Series

Mates With

[2139](#) KK Crimp Housing, [41695](#) KK Crimp Housing, [6442](#) KK Crimp Housing, [2145](#) PCB Connector, [41815](#) PCB Connector, [3069](#) KK Crimp Housing

Current - Maximum per Contact	7.0A
Voltage - Maximum	250V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235
Material Info	
Engineering Number	41662-B11A241
Reference - Drawing Numbers	
Packaging Specification	PK-41662-001-001
Product Specification	PS-08-50-001
Sales Drawing	SD-41662-001-001, SD-41662-001-002
Symbol/Footprint Data	SYM-26-48-1112-001

This document was generated on 11/25/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[26-48-2112](#)