


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0134210007](#)
Status: **Active**
Overview: [Asset Tracking Solutions](#)
Description: Alien Enterprise 4-port Fixed RFID Reader with Multi-Reader Management, 4 Additional Readers Supported, 920-925 MHz, for China and Singapore



Series image - Reference only

Documents:
[Datasheet \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	RFID Products
Series	13421
Comments	Includes Reader ONLY. No PoE/DC Power Supply Included.
Component Type	Fixed RFID Reader
Kit Option	Reader Only
LAN Protocols	TCP/IP,NTP,DNS,DHCP,SNMP
Market	China, Singapore
More Detailed Tech Information	For detailed product and compliance certification information, please https://www.alientechnology.com/download/alr-f800-x-documents/?wpd mdl=8100&ind=MTU2MjA4NjY5M3dwZG1fQUxSLUY4MDAtWCAoMjA0OCCWNC0xMSU0RmVhbnQ=.
Overview	Alien Datasheet .
Product Name	Alien
RFID Standard	EPC C1 Gen 2,ISO 18000-6c
Reader Protocols	ARP,LLRP
Type	Enterprise w/Multi-Reader Mgmt
UPC	193264421558
Physical	
Additional Readers Supported	Up to 4
Antennas	Up to 4 Supported
Communications	LAN TCP/IP (RJ-45), RS-232 (DB-9 F), USB Console, USB Host
Dimensions	202.00 x 191.00 x 28.00mm
General Purpose I/O	4 in / 8 out (Isolated)
Memory	1 GB RAM,2 GB Flash
Operating System	Linux
Packaging Type	Carton
Software SDK	Java,.NET,Ruby APIs
Temperature Range - Operating	-20° to +50°C
Electrical	
Frequency	920-925 MHz
Max Conductive RF Power (dBm)	30.7
Power Source	PoE,AC/DC Power Converter
Material Info	
Engineering Number	F800-CHN-X-RDRONLY

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[13421 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[13421-0007](#)