



OPTION D

- NOTES:
- MATERIAL:
HOUSING: POLYESTER(PBT), GLASS FILLED, UL94 V-0;
COLOR: BLACK
TERMINAL: PHOSPHOR BRONZE
 - FINISH:
30 GOLD: 0.76 MICROMETERS/30 MICROINCHES MINIMUM GOLD IN
1.91 MICROMETERS/75 MICROINCHES MINIMUM TIN
OVER NICKEL UNDERPLATE OVERALL
 - TO BE USED WITH 26 AWG STRANDED WIRE WITH (1.35)/.053
DIAMETER MAXIMUM INSULATION
 - SEE TABLE FOR AVAILABLE CIRCUIT SIZES
 - STANDARD PACKAGING PER PK-70873-0001. OPTIONAL PACKAGING
MAY BE AVAILABLE, REQUEST DRAWING PK-70400
 - PARTS STACKABLE END TO END ON (2.54)/.100 CENTERS
 - PRODUCT SPECIFICATION: PS-70400
 - SEE DRAWING SDA-70400-**** (SHEET 3) FOR OPTIONAL
HOUSING DETAILS
 - 4 CIRCUIT SHOWN. 3-25 CIRCUITS HAVE 2 RIBS
 - TO MATE WITH MOLEX PART NUMBERS: 70004-**** & 70013-****
 - 2 CIRCUIT ASSEMBLIES SUPPLIED AS GROUPED PAIRS

CKT. SIZE	A	B	EDP. NO.
2	(2.54) .100	(5.05) .199	I4-56-4023
3	(5.08) .200	(7.59) .299	I4-56-4033
4	(7.62) .300	(10.13) .399	I4-56-4043
5	(10.16) .400	(12.67) .499	I4-56-4053
6	(12.70) .500	(15.21) .599	I4-56-4063
7	(15.24) .600	(17.75) .699	I4-56-4073
8	(17.78) .700	(20.29) .799	I4-56-4083
9	(20.32) .800	(22.83) .899	I4-56-4093
10	(22.86) .900	(25.37) .999	I4-56-4103
11	(25.54) 1.000	(27.91) 1.099	I4-56-4113
12	(27.94) 1.100	(30.45) 1.199	I4-56-4123
13	(30.48) 1.200	(32.99) 1.299	I4-56-4133
14	(33.02) 1.300	(35.53) 1.399	I4-56-4143
15	(35.56) 1.400	(38.07) 1.499	I4-56-4153
16	(38.01) 1.500	(40.61) 1.599	I4-56-4163
17	(40.64) 1.600	(43.15) 1.699	I4-56-4173
18	(43.18) 1.700	(45.69) 1.799	I4-56-4183
19	(45.72) 1.800	(48.23) 1.899	I4-56-4193
20	(48.26) 1.900	(50.77) 1.999	I4-56-4203
21	(50.80) 2.000	(53.31) 2.099	I4-56-4213
22	(53.34) 2.100	(55.85) 2.199	I4-56-4223
23	(55.88) 2.200	(58.39) 2.299	I4-56-4233
24	(58.42) 2.300	(60.93) 2.399	I4-56-4243
25	(60.96) 2.400	(63.47) 2.499	I4-56-4253




I.D. SLOT CODE TO WIRE GAUGE CHART	
I.D. SLOT CODE	WIRE GAUGE
B	26 AWG.


PLATING CODE (STRIPE ON CARRIER STRIP)	
PLATING	COLOR
30 GOLD	RED



SECTION C-C



PRE-LOADED
ASSEMBLY



FINAL
ASSEMBLY

WIRE (SEE NOTE 3)

REMOVE ENG NO. EC NO: UCP2011-1110 TDRW:MSI BARRA 2010/10/19 CHKD:JORGAN 2010/10/19 APPR:SMILLER 2010/11/24	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION			
				MM/IN			INCH				
				mm	INCH	DRAWN BY		DATE		TITLE	
						MSI BARRA		2010/10/19		ASSEMBLY, SL CONNECTOR SINGLE ROW 2.54/.100 GRID	
						CHECKED BY		DATE			
				WAZ		1984/10/10					
				APPROVED BY		DATE		MOLEX MOLEX INCORPORATED			
				SMILLER		2010/11/24					
				MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
				SEE TABLE		SDA-70400-1296-1319		1 OF 1			
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[14-56-4103](#)