

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0151330205](#)
Status: **Active**
Overview: Pico-Clasp Wire-to-Board Connectors
Description: Pico-Clasp-to-Pico-Clasp Off-the-Shelf (OTS) Cable Assembly, Single Row, 450.00mm Length, 2 Circuits, White



Documents:
[3D Model](#) [Datasheet \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[3D Model \(PDF\)](#)

General
Product Family Cable Assemblies
Series [15133](#)
Application Signal, Wire-to-Board
Assembly Configuration Dual Ended Connectors
Connector to Connector Pico-Clasp-to-Pico-Clasp
Overmolded No
Overview [Pico-Clasp Wire-to-Board Connectors](#)
Product Name Pico-Clasp
Type Discrete Wire Assembly
UPC 191128138284

Physical
Cable Length 450.00mm
Circuits (Loaded) 2
Color - Resin White
Gender Female-Female
Lock to Mating Part Yes
Material - Metal Phosphor Bronze
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Nylon
Net Weight 1.100/g
Number of Rows 1
Packaging Type Bag
Pitch - Mating Interface 1.00mm
Plating min - Mating 1.000µm
Plating min - Termination 1.000µm
Single Ended No
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 0.60mm
Wire Size AWG 28
Wire/Cable Type UL 1571

Electrical
Current - Maximum per Contact 1.0A
Voltage - Maximum 50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers
Sales Drawing 2012341662-000

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[15133](#) Series

Mates With
Pico-Clasp Vertical Header [501331](#) , [504449](#) , [203556](#) , [203557](#) . Pico-Clasp Right-Angle Header [501568](#) , [202396](#) , [203558](#) , [203559](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15133-0205](#)