

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0151330303

Status:

Active

Overview:

Pico-Clasp Wire-to-Board Connectors

Description:

Pico-Clasp-to-Pico-Clasp Off-the-Shelf (OTS) Cable Assembly, Single Row, 300.00mm Length, 3 Circuits, White

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Assembly Configuration

Connector to Connector

Overmolded

Overview

Product Name

Type

UPC

Cable Assemblies

15133

Signal, Wire-to-Board

Dual Ended Connectors

Pico-Clasp-to-Pico-Clasp

No

Pico-Clasp Wire-to-Board Connectors

Pico-Clasp

Discrete Wire Assembly

191128138918

Physical

Cable Length

Circuits (Loaded)

Color - Resin

Gender

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Packaging Type

Pitch - Mating Interface

Plating min - Mating

Plating min - Termination

Single Ended

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire/Cable Type

300.00mm

3

White

Female-Female

Yes

Phosphor Bronze

Tin

Tin

Nylon

1.118/g

1

Bag

1.00mm

1.000µm

1.000µm

No

Crimp or Compression

0.60mm

28

UL 1571

Electrical

Current - Maximum per Contact

Voltage - Maximum

1.0A

50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Sales Drawing

2012341663-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

15133 Series

Mates With

Pico-Clasp Vertical Header [501940](#) , [203560](#)
, [203561](#) . Pico-Clasp Right Angle Header
[501953](#) , [203562](#) , [203563](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

15133-0303