

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190220009

Status:

Active

Overview:

Standard Quick-Disconnect Terminals

Description:

Krimptite Quick Disconnect, Male, for 18-22 (0.80-0.35mm²) Wire, Mylar Tape, Tab 4.75 x 0.51mm

Documents:

3D Model

Product Specification PS-19902-011-001 (PDF)


3D Model (PDF)

Product Specification PS-19902-015-001 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Product Specification PS-19902-005-001 (PDF)



Series image - Reference only

Agency Certification

CSA	LR18689
UL	E79133

General

Product Family	Quick Disconnects
Series	19022
Comments	Economical
Crimp Quality Equipment	Yes
Insulated	No
Overview	Standard Quick-Disconnect Terminals
Product Name	Krimptite
Type	Quick Disconnect
UPC	800753039537

Physical

Barrel Type	Closed
Gender	Male
Glow-Wire Capable	No
Insulation	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Zinc Chromate
Material - Plating Termination	Zinc Chromate
Net Weight	0.495/g
Orientation	Straight
Packaging Type	Adhesive Tape on Reel
Polarized to Mating Part	No
Tab Thickness	0.51mm
Tab Width	4.75mm
Temperature Range - Operating	Per Wire Specification
Wire Size AWG	18, 20, 22

Electrical

Voltage - Maximum	Per Wire Specification
-------------------	------------------------

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	AMCT-17T
--------------------	----------

Reference - Drawing Numbers

Product Specification	PS-19902-005-001, PS-19902-011-001, PS-19902-015-001
Sales Drawing	SD-19022-017-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)
1,2-
Benzenedicarboxylic
acid, bis(3-
methylbutyl)
Disodium 3,3'-[[1,1'-
Biphenyl]-4,4'-
Diylbis(Azo)
Octamethylcyclotetrasiloxane
Decamethylcyclopentasiloxane
Dodecamethylcyclohexasiloxane
Octanoic acid,
2,2,3,3,4,4,5,5,6,6,7,7,8,8,8-
pen
Benzo(ghi)perylene
Dipentyl phthalate
Imidazolidine-2-thione
Phenanthrene
N,N-
Dimethylformamide
4-aminoazobenzene
[Phthalato(2-)]dioxotrilead
Silicic acid (H2Si2O5),
barium salt (1:1),
lead-
Sulfurous Acid, Lead
Salt, Dibasic
Cyanamide, lead(2+)
salt (1:1)
Lead titanium
zirconium oxide
Dioxobis(stearato)trilead
Tetralead-trioxide-
sulphate
Pentalead-tetraoxide-
sulphate
Lead-titanium-trioxide

China RoHS

Lead-dinitrate
Cadmium
Lead
Lead(II,IV)-oxide
Cadmium-oxide
Diboron-trioxide
Decabromodiphenylether
1,2-bis(2-methoxyethoxy)ethane
1,2-Dimethoxyethane
bis(2-methoxyethyl) ether
Tris(2-chloroethyl) phosphate
Lead chromate
molybdate sulfate red
Lead chromate
Bis(tributyltin) oxide
Alkanes, C10-13, chloro
Cobalt-dichloride
Perfluorohexane-1-sulphonic acid and its salts
Perfluorononan-1-oic acid
(2,2,3,3,4,4,5,5,6,6,7-Dioctyltin dilaurate, stannane, dioctyl-, bis(co
Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]o
Pyrene
Fluoranthene
Perfluorobutane sulfonic acid (PFBS) and its sal
Tris(4-nonylphenyl, branched and linear) phosphi
Nonadecafluorodecanoic acid (PFDA) and its sodiu
Zirconia
Aluminosilicate
Refractory Ceramic
Fibr
1,2-Benzenedicarboxylic acid, dipentyl ester, br diisohexyl phthalate
1,2-Benzenedicarboxylic acid, dihexyl ester, bra
2-(2H-Benzotriazol-2-yl)-4-(tert-butyl)-6-(sec-b
2-(2H-Benzotriazol-2-yl)-4,6-ditertpentylphenol
Dibutylbis(pentane-2,4-dionato-O,O')tin
2-ethylhexyl 10-ethyl-4,4-dioctyl-7-oxo-8-oxa-3,

Phenol, 2-(2H-benzotriazol-2-yl)-4,6-bis(1,1-dim
Ammonium-pentadecafluorooctanoate
C.I. Direct Black 38
Dibutyltin-dichloride
1,2-diethoxyethane
Halogen-Free
Status
Low-Halogen
For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[19022](#) Series

Application Tooling | [FAQ](#)
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	190270071

This document was generated on 09/13/2021
PLEASE CHECK [WWW.MOLEX.COM](#) FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19022-0009](#)