


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:	0190700131
Status:	Active
Overview:	Solderless Terminals
Description:	InsulKrimp Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 10 (M5), Length 31.60mm, Mylar Tape Carrier

Documents:

3D Model	Product Specification PS-19902-011-001 (PDF)
Drawing (PDF)	Product Specification PS-19902-015-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-19902-009-001 (PDF)	



Series image - Reference only

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Ring and Spade Terminals
Series	<u>19070</u>
Crimp Quality Equipment	Yes
Overview	<u>Solderless Terminals</u>
Product Name	InsulKrimp
Type	Ring
UPC	800753069770

Physical

Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-0
Insulation	PVC
Material - Plating Mating	Tin
Net Weight	0.659/g
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	2.540μm
Plating min - Termination	2.540μm
Stud Size	10 (M5)
Wire Insulation Diameter	6.40mm max.
Wire Size AWG	10, 12

Material Info

Engineering Number C-230-10XT

Reference - Drawing Numbers

Product Specification	PS-19902-009-001, PS-19902-011-001, PS-19902-015-001
Sales Drawing	SD-19070-007-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

19070 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press Mini-Mac Pneumatic Applicator for Industrial Terminals 6-26 AWG	<u>192880179</u> <u>638851500</u>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19070-0131](#)