

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191600028](#)
Status: **Active**
Overview: [Splices](#)
Description: Closed-End Insulated Splice for 8 AWG Wire, Tape and Reel

Documents:

Drawing (PDF)	Packaging Specification PK-19408-109-001 (PDF)
Product Specification PS-19902-015-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Splices
Series	19160
Crimp Quality Equipment	Yes
Overview	Splices
Product Name	Closed-End Insulated
UPC	800753110335

Physical

Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-2
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	2.290/g
Packaging Type	Adhesive Tape on Reel
Temperature Range - Operating	105°C
Wire Insulation Diameter	12.19mm max.
Wire Size AWG	8

Electrical

Voltage - Maximum	600V
-------------------	------

Material Info

Engineering Number	NC-8T
--------------------	-------

Reference - Drawing Numbers

Packaging Specification	PK-19408-109-001
Product Specification	PS-19902-015-001
Sales Drawing	PS-19160-008-001, SD-19160-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[19160 Series](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	192880245

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19160-0028](#)