

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0192150050

Status:

Active

Overview:

[Splices](#)

Description:

VersaKrimp Parallel Splice for 4/0 AWG Wire

Documents:

[Drawing \(PDF\)](#)

[Product Specification PS-19902-011-001 \(PDF\)](#)

[Product Specification PS-19902-013-001 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL

E32244

General

Product Family

Splices

Series

19215

Crimp Quality Equipment

Yes

Overview

[Splices](#)

Product Name

Parallel, VersaKrimp

UPC

800755062700

Physical

Barrel Type

Closed - Brazed

Insulation

None

Material - Metal

Copper

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Net Weight

25.628/g

Packaging Type

Bag

Wire Size AWG

4/0

Material Info

Engineering Number

L-379

Reference - Drawing Numbers

Product Specification

PS-19902-011-001, PS-19902-013-001

Sales Drawing

SD-19205-007-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19215 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Die Set (large) for the HHLS Hydraulic Crimper	192900031
Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals	192940008
Hydraulic Dieless Crimping Tool	638161700
Square "Din" Style Die Set for BCL and VersaKrimp Un-insulated Ring Tongue Terminals	640038370

This document was generated on 09/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

19215-0050