

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0307001189

Status:


Active

Overview:

H-DAC 64 Unsealed Connector System

Description:

2.54mm Pitch, 0.64mm Width H-DAC 64 High Density Automotive Connectors, Dual Row, Female Harness Assembly, 18 Circuits, Polarization Option 3, Natural



Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-30700-0001-001 (PDF)

Product Specification PS-30968-0001-001 (PDF)

Packaging Specification PK-30907-417-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	30700
Application	Automotive, Power, Wire-to-Board, Wire-to-Wire
Comments	Polarization Option 3
Overview	H-DAC 64 Unsealed Connector System
Product Name	H-DAC 64
UPC	822348517213
Physical	
Circuits (maximum)	18
Color - Resin	Natural
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene Alloy, Polyester
Net Weight	4.861/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +100°C
Electrical	
Current - Maximum per Contact	7.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-30907-417-001
Product Specification	PS-30700-0001-001, PS-30968-0001-001
Sales Drawing	SD-30700-120-001

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Not Relevant

For more information, please visit

Contact US

China ROHS

ELV

RoHS Phthalates

Not Relevant

Compliant

Not Contained

Search Parts in this Series

30700 Series

Mates With

H-DAC 64 Header 307004186 , 307004189 , 307005186 , 307005189 , Crimp Housing 30968

Use With

Contact Molex for Terminal information.

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

30700-1189