

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0330000002](#)
Status: **Active**
Overview: [MX150 Sealed and Unsealed Connector System](#)
Description: MX150 Male Terminal for Mat-Sealed or Unsealed Connectors, Tin Plating, 16, 18 and 20 AWG, Right Reel Payoff

Documents:

Drawing (PDF)	Packaging Specification 313025040-000 (PDF)
Product Specification PS-33012-002-001 (PDF)	Test Summary TS-33000-001-001 (PDF)
Application Specification AS-33000-001-001 (PDF)	Datasheet (PDF)
Application Specification AS-33000-001-CH-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-33000-001-FR-001 (PDF)	

General

Product Family	Crimp Terminals
Series	33000
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	For automatic and semi-automatic crimping, use Left Reel Payoff terminals. See Sales Drawing for Left Reel Payoff Part Numbers.
Crimp Quality Equipment	Yes
Overview	MX150 Sealed and Unsealed Connector System
Product Name	MX150
UPC	800756103556

Physical

Gender	Male
Grip Code	18
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.320/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.54mm max.
Wire Size AWG	16, 18, 20
Wire Size mm²	0.75-1.00

Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	14V DC

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-33000-001-001, AS-33000-001-CH-001, AS-33000-001-FR-001
Packaging Specification	313025040-000
Product Specification	PS-33012-002-001
Sales Drawing	SD-33000-001-001
Test Summary	TS-33000-001-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS

ELV

RoHS Phthalates

Green Image

Compliant

Not Contained

Search Parts in this Series

[33000](#) Series

Use With

[33482](#) Dual Row Housing, [33481](#) Single Row Housing, [33486](#) Hybrid Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Toolkit for MX150 Connectors	2002220700
FA2 Mechanical Feed Applicator for MX150 Mat Seal/ Unsealed Blade Terminals, 16 AWG TXL Wire and 18 AWG GXL Wire	638084100

FA2 Pneumatic Feed 638084110
Applicator for MX150
Mat Seal/Unsealed
Blade Terminals, 16
AWG TXL Wire and
18 AWG GXL Wire
PremiumGrade 638112400
Hand Crimp
Tool for 1.50mm
MX150 Blade Male
Terminals, 14-16
AWG
PremiumGrade 638112600
Hand Crimp
Tool for 1.50mm
MX150 Blade Male
Terminals, 18-22
AWG
Extraction Tool for 638131500
MX150L, MX150, PT
Bulb Socket, iGrid,
SPOX, and Wire-to-
Motor Terminals

This document was generated on 09/13/2021
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[33000-0002](#)