

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0330123004

Status:

Active

Overview:

MX150 Sealed and Unsealed Connector System

Description:

MX150 Female Terminal for Mat-Sealed Connectors, Tin Plating, Grip Code M3, Preferred Terminal for use in Sealed Application with 0.35-0.50mm², Left Reel Payoff, Contact Material Thickness 0.30mm²



Series image - Reference only

Documents:	
Drawing (PDF)	Application Specification AS-33012-002-FR-001 (PDF)
Product Specification PS-33012-002-001 (PDF)	Packaging Specification 313025040-000 (PDF)
Application Specification 330120000-AS-KR-000 (PDF)	Test Summary TS-33012-002-001 (PDF)
Application Specification AS-33012-002-001 (PDF)	Datasheet (PDF)
Application Specification AS-33012-002-CH-001 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	33012
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Left Reel Payoff, Small Polarization Rib
Crimp Quality Equipment	Yes
Overview	MX150 Sealed and Unsealed Connector System
Product Name	MX150
UPC	884982250826
Physical	
Gender	Female
Grip Code	M3
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.390/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.70mm max.
Wire Size AWG	N/A
Wire Size mm²	0.35-0.50
Electrical	
Current - Maximum per Contact	Contact Molex
Voltage - Maximum	14V DC
Material Info	
Reference - Drawing Numbers	
Application Specification	330120000-AS-KR-000, AS-33012-002-001, AS-33012-002-CH-001, AS-33012-002-FR-001
Packaging Specification	313025040-000
Product Specification	PS-33012-002-001
Sales Drawing	SD-33012-002-001, SD-33481-0001-001
Test Summary	TS-33012-002-001

EU ELV
Compliant

EU RoHS
Compliant
REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free
Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
33012 Series

Use With
33472 Dual Row Housing. 33476 Hybrid Housing. 33471 Single Row Housing

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction Toolkit for MX150 Connectors	2002220700
FA2 Mechanical Feed Applicator for MX150 Female Terminals, 0.35mm² and 0.50mm² ISO Wire	638082500
Extraction Tool for MX150L, MX150, PT	638131500

Bulb Socket, iGrid,
SPOX, and Wire-to-
Motor Terminals
Hand Crimp Tool for 638233700
ISO (M3) Receptacle
Terminals
FineAdjust Applicator639041200
for SRC Connector
using MX150
Receptacle
Terminals, 0.50mm²
wires

This document was generated on 10/01/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[33012-3004](#)