

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0347072022

Status:

Active

Overview:

Stac64 Single, Multi-Pocket and Hybrid Header System

Description:

Stac64 2 Bay Vertical Headers, 30 Circuits, Bay A 20 Circuit Signal Header, Polarization C, Brown; Bay B 10 Circuit, Power Header, Polarization A, Black, Tray



Series image - Reference only

Documents:	
3D Model	Application Specification AS-34729-020-001 (PDF)
3D Model (PDF)	Packaging Specification PK-31300-892-001 (PDF)
Drawing (PDF)	Brochure (PDF)
Product Specification PS-31372-100-001 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	34707
Application	Automotive, Power, Wire-to-Board
Comments	Bay A 20 Circuits Stac64 Vertical Signal Header, Polarization C. Bay B 10 Circuits Stac64 Vertical Power Header, Polarization A
Overview	Stac64 Single, Multi-Pocket and Hybrid Header System
Product Name	Stac64
UPC	883906170073
Physical	
Breakaway	No
Circuits (Loaded)	30
Circuits (maximum)	30
Color - Resin	BLACK BROWN
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	16.107/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.36mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Packaging Type	Tray
Pitch - Mating Interface	2.30mm, 2.54mm, 3.50mm, 5.25mm
Pitch - Termination Interface	2.30mm, 2.54mm, 3.50mm, 5.25mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +100°C
Termination Interface: Style	Through Hole

Electrical

EU ELV	
Compliant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Contained Per - D(2021)4569-DC (8 July 2021)	
Boric acid	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

34707 Series

Mates With

[31408](#) USCAR 2.54mm (.100") Pitch Receptacle, [31372](#) 5.25mm (.206") Pitch Hybrid Receptacle Assembly, [34729](#) 2.54mm (.100") Pitch Stac64 Right Angle Receptacle

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	500V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	040
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-34729-020-001
Packaging Specification	PK-31300-892-001
Product Specification	PS-31372-100-001
Sales Drawing	SD-34707-200-001

This document was generated on 09/20/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34707-2022](#)