

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0465574245](#)
Status: **Active**
Overview: [SEARAY and SEARAY Slim Mezzanine Family](#)
Description: SEARAY Slim Receptacle, 160 Circuits, 6.00mm Unmated Height, 4 Rows, with Pegs, Solder Charge Lead-Free

Documents:

3D Model	Application Specification AS-45970-002-001 (PDF)
Drawing (PDF)	Application Specification AS-45970-990-001 (PDF)
3D Model (PDF)	Packaging Specification PK-45971-002-001 (PDF)
Product Specification PS-45970-001-001 (PDF)	Test Summary TS-45970-002-001 (PDF)
Product Specification TS-45970-001-001 (PDF)	Symbol Footprint Data SYM-46557-4245-001 (PDF)
Application Specification AS-45970-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification


CSA	LR19980
UL	E29179

General

Product Family	PCB Receptacles
Series	46557
Application	Board-to-Board, Signal
Electrical Model	Yes
Overview	SEARAY and SEARAY Slim Mezzanine Family
Product Name	SEARAY
UPC	883906530518

Physical

Circuits (Loaded)	160
Circuits (maximum)	160
Color - Resin	Black
Durability (mating cycles max)	100
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	No
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2.171/g
Number of Rows	4
Orientation	Vertical
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	2.18mm
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Robotic Placement	Pick and Place Cap
Stackable	No
Surface Mount Compatible (SMC)	Yes



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[46557](#) Series

Mates With

[46556](#) SEARAY Slim Plug

Temperature Range - Operating	-55° to +125°C
Termination Interface: Style	Surface Mount
Unmated Height	8.00mm
Electrical	
Current - Maximum per Contact	2.7A
Grounding to PCB	No
Voltage - Maximum	240V AC
Solder Process Data	
Duration at Max. Process Temperature (seconds)	020
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-45970-001-001, AS-45970-002-001, AS-45970-990-001
Electrical Model Document	EE-45970-010-010
Packaging Specification	PK-45971-002-001
Product Specification	PS-45970-001-001, TS-45970-001-001
S-Parameter Model	SP-45970-010-010
Sales Drawing	SD-46557-001-001
Symbol/Footprint Data	SYM-46557-4245-001
Test Summary	TS-45970-002-001

This document was generated on 09/09/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

46557-4245